



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.3% in BODY & NUT) Cd (3% in BODY & NUT) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #CAT-55A-TC-H12
General Purpose Hookup Wire: Tin Coated Copper Wire, 12 AWG



TE Part #CM6170-000
0024A0311-9



TE Part #1062-20-0322
SOC, SF, SIZE 20, 16-22, SLEVELESS, NI /NI




TE Part #331003-005
55A1111-22-9-9




TE Part #625160-000
D-110-41




TE Part #F345203001
RAY-101-3.0(100)



TE Part #820057-000
322A112-25-0



TE Part #823693-000
322A123-25-0



TE Part #782251-000
TXR21AB00-1005AI

Documents

Product Drawings

208M914-19B10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_128431-000_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_128431-000_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_128431-000_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



5-1654025-5_sec6_Adapters

English

Product Specifications

General Information Package for Solid, Spin Coupling and Shielded Adapters

English

General Harness Repair Manual

English

Product Specification

English