

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** LED2WORK GmbH.

**Supplier's address:** Vertrieb, Stuttgarter Straße 13A, 75179 Pforzheim, DE

**Model identifier:** 2941-5001-00-LE-332p

## Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	-		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No


## Product parameters

Parameter	Value	Parameter	Value
<b>General product parameters:</b>			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	17	Energy efficiency class	D
Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	2 204 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	5 600
On-mode power ( $P_{on}$ ), expressed in W	16,8	Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal	0,00
Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	85
Outer dimensions without separate control gear, lighting control	Height	7	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	332	
	Depth	14	
			See image in last page

parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power <sup>(a)</sup>	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,329 0,324
<b>Parameters for directional light sources:</b>			
Peak luminous intensity (cd)	1 240	Beam angle in degrees, or the range of beam angles that can be set	117
<b>Parameters for LED and OLED light sources:</b>			
R9 colour rendering index value	0	Survival factor	-
the lumen maintenance factor	-		


(a) : not applicable;

(b) : not applicable;



Spektrum

Model placed on the Union market from 20/08/2021



**EPREL registration number:** 775845

<https://eprel.ec.europa.eu/qr/775845>

**Supplier:** LED2WORK GmbH (Manufacturer)

**Website:** [led2work.com](https://led2work.com)

**Customer care service:**

**Name:** Vertrieb

**Website:** [www.led2work.com](https://www.led2work.com)

**Email:** [info@led2work.com](mailto:info@led2work.com)

**Phone:** +49 7231 44920-00

**Address:**

Stuttgarter Straße 13A

75179 Pforzheim

Germany