
## KEMET Part Number: R82CC4220Z370K



## R82, Film, Metallized Polyester Stacked, Automotive Grade, 2.2 uF, 10%, 50 VDC, 85°C, Lead Spacing = 5mm



Dimensions		
L	7.2mm +0.3mm	
Н	11mm +0.1mm	
Т	6mm +0.1mm	
S	5mm +/-0.4mm	
LL	17mm +1/-2mm	
F	0.5mm +/-0.05mm	

Packaging Specifications		
Packaging:	Bulk, Bag	
Packaging Quantity:	1000	

General Information	
Supplier:	KEMET
Series:	R82
Dielectric:	Metallized Polyester Stacked
Style:	Radial
Features:	Automotive Grade, DC Multipurpose Applications
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C

Specifications		
Capacitance:	2.2 uF	
Capacitance Tolerance:	10%	
Voltage AC:	30 VAC	
Voltage DC:	50 VDC	
Temperature Range:	-55/+105C	
Rated Temperature:	85°C	
Dissipation Factor:	0.80% 1kHz, 1.20% 10kHz	
Insulation Resistance:	454.5 MOhms	
Max dV/dt:	100 V/us	
Inductance:	7 nH	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

