




XFP

TE Internal #: 1489948-2

XFP Heat Sink, 10 W / 15 W / 5 W, XFP

[View on TE.com >](#)

Connectors > Connector Accessories > Heat Sinks



Device Type: XFP

Power Rating: 5 W, 10 W, 15 W

Features

Product Type Features

Device Type	XFP
-------------	-----

Electrical Characteristics

Power Rating	5 W, 10 W, 15 W
--------------	-----------------

Body Features

Primary Product Material	Copper Alloy
Primary Product Plating Material	Tin

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2303922-2
HEAT SINK SFP DWDM 4.2mm TALL



TE Part # 1542618-2
XFP MSA SAN APPLICATION



TE Part # 1829905-2
HEAT SINK SFP DWDM 13.5mm TALL



TE Part # 1829904-2
HEAT SINK SFP DWDM 6.5mm TALL



TE Part # CAT-X29-C1171XN
XFP Cage Assemblies and Kits



TE Part # 1963850-2
XFP. MSA HEATSINK 10mm TALL



TE Part # 1542706-3
XFP. MSA NETWORK APPLICATION H




TE Part # 1542993-2
SFP HEATSINK 13.5MM TALL




TE Part # 1963854-2
HEAT SINK SFP DWDM 10.0mm TALL

Also in the Series | **XFP**



Connector Caps & Covers(1)



Heat Sinks(8)



Pluggable IO Connectors & Cages(25)



XFP(25)

Customers Also Bought



TE Part #2288221-1
CFP2 EMI/DUST PLUG



TE Part #1-6450871-0
MBXLE R/A RCPT 20S+6P



TE Part #2007215-2
SFP+ 1x1 Cage Assy, PCI, Press Fit




TE Part #2007464-3
SFP+ 1x1 Cage Assy, PF,with Heatsink



TE Part #1879075-4
THS25 R10 5%



TE Part #1542706-3
XFP. MSA NETWORK APPLICATION H



TE Part #1892200-5
MBXLE R/A HDR 2P+24S+2P solder



TE Part #2319224-6
zSFP+ STACKED 2X6 RECEPTACLE ASSEMBLY



TE Part #2274157-5
SFP+ assy 2x2 Spring Fingers 4 LP Sn



TE Part #1393280-5
V23086C1001A402

Documents

Product Drawings

[XFP HEAT SINK CLIP, PLATED](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_1489948-2_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_1489948-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1489948-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1773408-1 Pluggable Input/Output Solutions catalog - XFP section](#)

English

[1-1773717-7_PLUGGABLE_IO_QRG_CN](#)

English

[1-1773717-8_PLUGGABLEIO_QRG_TCN](#)

English

[1-1773717-9_HIGH_SPEED_IO_QRG_JA](#)

English

Product Specifications

[Application Specification](#)

English