#### AMP | AMP CPC


TE Internal #: 182663-1

AMP CPC, Unscreened Circular Connector Backshells & Clamps, Cable Clamp, Size 13, Straight, Individual, 3/4-20 UNEF-2B

View on TE.com >



Connectors > Circular Connectors > Circular Connector Accessories > Unscreened Circular Connector Backshells & Clamps > CPC CABLE CLAMPS EMEA



Backshell & Clamp Accessory Type: Cable Clamp

Compatible With Circular Connector Shell Size: 13

Body Orientation: Straight

Accepts Cable Diameter (Max): 11.51 mm [ .453 in ]

Protective Cover: Without

#### All CPC CABLE CLAMPS EMEA (5)

#### **Features**

#### **Product Type Features**

Product Type	Accessory	
Backshell & Clamp Accessory Type	Cable Clamp	
Protective Cover	Without	
Body Features		

Cable Clamp Material	Thermoplastic
Cable Clamp Flammability Rating	UL 94V-0
Cable Clamp Color	Black

#### Mechanical Attachment

	2/4 20 LINEE 2D
Screw & Hole Thread Size	3/4-20 UNEF-2B

#### **Housing Features**

#### **Dimensions**

Accepts Cable Diameter (Max)	11.51 mm[.453 in]	

#### Operation/Application

### **Packaging Features**



Packaging Quantity	100
Packaging Method	Individual

### **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## Compatible Parts



Also in the Series | AMP CPC







Circular Connector Boots & Strain

Relief(6)



Circular Connector Caps & Covers(16)

Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Connector Seals(36)




Circular Power Connectors(512)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

# Customers Also Bought







CPC 13-9 FREE HANGING RECPT

TE Part #206705-2





### **Documents**



### **Product Drawings**

13 SIZE CPC STD CLAMP

English

**CAD Files** 

3D PDF

English

**Customer View Model** 

ENG\_CVM\_182663-1\_C.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_182663-1\_C.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_182663-1\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

## Product Environmental Compliance

**Product Compliance** 

English

**Product Compliance** 

English