

Features


- Potable water applications up to +23°C
- WRAS-approved for safe use with drinking water
- Suitable for general sealing and gasketing
- Excellent weather resistance, durability, and chemical resistance
- High tensile strength (9 MPa) and good compression set resistance
- Resists various chemicals commonly encountered in water and industrial applications
- Cloth/Cloth effect finish

RS PRO Black EPDM WRAS Approved Rubber Sheet

1m x 1.6m x 3mm

+100°C to -15°C

RS Stock No.: 0205550



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

*The RS PRO Ethylene Polypropylene (EPDM) rubber sheet is suitable for a wide range of applications including gaskets and seals in potable water systems, food processing equipment, chemical processing equipment and roofing and construction.*

General Specifications

|                  |                                          |
|------------------|------------------------------------------|
| Colour           | Black                                    |
| Material         | Ethylene Polypropylene (EPDM)            |
| Adhesive Backing | No                                       |
| Suitability      | WRAS approved for use with potable water |

Mechanical Specifications

|                  |        |
|------------------|--------|
| Length           | 1m     |
| Width            | 1.6m   |
| Thickness        | 3mm    |
| Elongation       | 450%   |
| Tensile Strength | 9 MPa  |
| Hardness         | 70 ShA |

Operation Environment Specifications

|                               |       |
|-------------------------------|-------|
| Maximum Operating Temperature | 100°C |
| Minimum Operating Temperature | -15°C |

Similar Products

| Stock No | Adhesive Backing | Thickness |
|----------|------------------|-----------|
| 0205551  | No               | 1.5mm     |
| 0205550  | No               | 3mm       |
| 0205552  | No               | 6mm       |