




Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors > Backplane Connector: Plug-in module



Number of Positions: 90  
Row-to-Row Spacing: 1.6 mm [ .06 in ]  
Mating Alignment: Without  
Number of Rows: 9  
Number of Columns: 10

[All Backplane Connector: Plug-in module \(30\)](#)

Features

Product Type Features

Signal Arrangement	Single Ended
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
PCB Connector Type	PCB Mount Header
Shroud Style	Partially Shrouded

Configuration Features

Backplane Architecture	Traditional Backplane
Number of Positions	90
Number of Rows	9
Number of Columns	10
PCB Mount Orientation	Right Angle
Guide Location	Center



Contact Features

Contact Current Rating (Max)	1.5 A
------------------------------	-------

Mechanical Attachment

Mating Alignment	Without
Connector Mounting Type	Panel Mount

Housing Features

Number of Shrouded Sides	4
Centerline (Pitch)	.08 mm[1.9 in]

Dimensions

Row-to-Row Spacing	1.6 mm[.06 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in




articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


## Customers Also Bought




TE Part #764619-000  
CWT-7-W122-5




TE Part #352171-1  
Z-PACK/B F-HDR. 95P




TE Part #7-1625999-8  
HSC100 R68 5%



TE Part #1757828-5  
AMPLIMITE,RCPT ASY,POSTD,109,ZN,5



TE Part #5177985-4  
0.8FH,R05H.5,100,08/Sn,TR,SC



TE Part #1053372-1  
2062 8001 90,OSM JACK, QPL

## Documents

### Product Drawings

Fortis Zd 10 Col R/A Full Shroud Assy SE

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2102318-1\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2102318-1\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2102318-1\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



Fortis Zd Connector Brochure

English

Fortis Zd LRM

English

---

Product Specifications

Application Specification

English