



Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP+**
Pluggable I/O Product Type: **Cage Assembly**
Sealable: **Yes**
Circuit Application: **Signal**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Form Factor	QSFP+
Pluggable I/O Product Type	Cage Assembly
Sealable	Yes

Configuration Features

Number of Rear EONs per Port Column	2
Number of Ports	4
Port Matrix Configuration	1 x 4

Electrical Characteristics

Data Rate (Max)	14 Gb/s
-----------------	---------

Body Features

Heat Sink Style	Pin
Heat Sink Finish	Anodized Black
	.165 in
Heat Sink Height Class	PCI

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----



Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.2 mm[.086 in]

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.45 mm[.057 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Elastomeric Gasket

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.2% in Component) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2829040-7 QSFP IB EDR, 26AWG, 2.0M	 TE Part # 2202165-5 QSFP TO QSFP, 26AWG, FDR, 5.0 METER	 TE Part # 2829040-8 QSFP IB EDR, 26AWG, 3.0M	 TE Part # 2202165-4 QSFP TO QSFP, 26AWG, FDR, 4.0 METER
 TE Part # 2053453-5 C/A, QSFP TO 4XSFP+, 4.0M	 TE Part # 1888810-2 EMI/Dust Cover,XFP And QSFP	 TE Part # 2829040-2 QSFP IB EDR, 33AWG, 1.0M	 TE Part # CAT-C11-H5011142 QSFP to QSFP I/O Cable Assembly: 33 AWG
 TE Part # 1-2053638-6 C/A, QSFP, 0.5M, P1-P2, UNEQUALIZED	 TE Part # 2821033-8 QSFP TO [4]SFP+, 28G, 1M, 33AWG	 TE Part # 2215057-1 ASSY, SEATING TL, QSFP 1X4	 TE Part # 2829040-4 QSFP IB EDR, 30AWG, 1.0M



TE Part # 2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part # 2829040-6
QSFP IB EDR, 30AWG, 2.0M




TE Part # CAT-C11-H50111
QSFP-Four SFP+ I/O Cable Assembly
30 AWG


Also in the Series | QSFP/QSFP+



Pluggable I/O Cable Assemblies(13)




Pluggable IO Connectors & Cages(154)




QSFP, QSFP+ & zQSFP+(154)

Customers Also Bought



TE Part #1888810-2
EMI/Dust Cover,XFP And QSFP




TE Part #103906-4
05 MTE HDR SRRA LATCH .100CL



TE Part #2065883-1
Zd Plus, 3 pair receptacle ass



TE Part #2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part #5103310-1
A/L LOW PRO HDR 10P RA BLACK



TE Part #60620-1
CMNL PIN 20-14 TPBR L/P



TE Part #487526-4
005 HOUSING FFC RCPT 100CL SR



TE Part #1-480426-0
04P CMNL CAP HSG F/H NATL



TE Part #2336682-1
2MM HM FEMALE ASSY, COL8



TE Part #5103309-1
A/L LOW PRO HDR 10P VERT BLACK



Documents

Product Drawings

1X4 CAGE ASSEMBLY, THRU BEZEL, W/ GASKET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2170287-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2170287-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2170287-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English