

# CFPT-9301, -9302 SMD TCVCXOs

# ISSUE 7; 1 NOVEMBER 2010 - RoHS 2002/95/EC Description

■ Surface mount temperature compensated voltage controlled crystal oscillators for medium to high volume applications where small size and high performance are prerequisites. Manufactured for us by Rakon utilising their Pluto™ ASIC technology and capable of sub 0.3ppm performance over an extended temperature range. Its ability to function down to a supply voltage of 2.4V and low power consumption makes it particularly suitable for mobile applications

#### **Standard Frequencies**

10 (HCMOS only), 12.688375, 12.8, 13, 14.4, 16, 16.367, 16.384, 16.8, 19.2, 19.44, 20, 24, 24.5535, 26, 32.768, 33.6, 36, 38.88, 40MHz

#### Frequency Range

■ 1.5 to 52MHz

#### Output Compatibility & Load (standard)

- HCMOS 15pF max
- Clipped sinewave 10kΩ // 10pF, DC-coupled

# Supply Voltage

- Standard 3.0V, 3.3V (see table)
- Supply voltages in the range 2.4 to 6.0V available to order, please contact our sales offices

## Supply Current (typically)

■ HCMOS

1+Frequency(MHz)\*Supply(V)\*{Load(pF)+15}\*10-3mA e.g. 20MHz, 3.3V, 15pF  $\approx$  3mA

 Clipped Sinewave 1+Frequency(MHz)\*1.2\*{Load(pF)+30}\*10-3 mA

e.g. 20MHz, 10pF ≈ 2mA

## Frequency Stability

- Temperature: see table
- Supply Voltage Variation, ±5%

HCMOS, <20MHz ±0.1ppm typ

HCMOS, 20-<35MHz ±0.3ppm typ

HCMOS, 35-52MHz ±0.5ppm typ

Clipped Sinewave ±0.05ppm typ

Load Coefficient

15pF ±5pF (HCMOS)

<20MHz ±0.2ppm typ

20-<35MHz ±0.3ppm typ

35-52MHz ±0.5ppm typ

 $10k\Omega$  //  $10pF \pm 10\% \pm 0.05ppm$  typ

#### Ageing

- ±1ppm maximum in 1st year, frequency ≤20MHz
- ±3ppm maximum for 10 years (including the first year), frequency ≤20MHz
- ±2ppm maximum in 1st year, frequency >20MHz
- ±5ppm maximum for 10 years (including the first year), frequency >20MHz

#### Frequency Adjustment - option A (standard)

Ageing adjustment by means of external Control Voltage applied to pad 1

- Range (frequency ≤ 20MHz) ≥ ±5ppm
- Range (frequency > 20MHz) ≥ ±7ppm
- Linearity ≤2%
- Slope Positive
- Input resistance ≥100kΩ
- Modulation bandwidth ≥2kHz
- Standard control voltage range 1.5V±1V

#### Frequency Adjustment - option B

No frequency adjustment

Initial calibration ≤ ±1.0ppm

#### Storage Temperature Range

■ -55 to 125°C

#### Environmental

- Shock: IEC 60068-2-27, Test Ea: 1500G acceleration for 0.5ms, 3 shocks in each of 3 mutually perpendicular planes
- IEC 60068-2-6 test Fc. 10-60Hz 1.5mm displacement, 60-2000Hz at 20G, 4 hours in each of three mutually perpendicular axes at 1 oct/min

#### Non Standard Requirements

 Non standard requirements may be available upon request, please contact our sales offices

#### Packaging

- Loose in bulk pack, 10pcs per pack
- Tape and reel in accordance with EIA-481-D, 1kpcs per reel (please see pages 372 & 373)

# Ordering Information (\*minimum required)

- Frequency\*
- Model\*
- Frequency Adjustment Option\*
- Output
- Frequency Stability (over operating temperature range)\*
- Operating Temperature Range\*
- Supply Voltage

#### Example

■ 20.0MHz CFPT-9301 A HCMOS ±1.0ppm -20 to 70C 3.3V






# **Electrical Specification - maximum limiting values**

Frequency Range	Supply Voltage	Output Waveform	Output Levels	Rise Time (t <sub>r</sub> )	Fall Time(tf)	Duty Cycle	Model Number
1.5 to 52.0MHz	3.3V±10%*	HCMOS 15pF	V <sub>0H</sub> ≥ 90% V <sub>S</sub> V <sub>0L</sub> ≤ 10% V <sub>S</sub>	8ns	8ns	45/55%	CFPT-9301
12.0 to 52.0MHz	3.0V±10%*	Clipped Sine 10kΩ//10pF	V <sub>pk-pk</sub> ≥0.8V	-	-	-	CFPT-9302
*Parts will operate corre	ectly with ±10% supply	voltage variation but s	upply coefficient is me	easured with ±5%	variation		

# Frequency Stabilities over Operating Temperature Range


Operating Temperature Ranges	Frequency Stabilities v Operating Temperature Range						
	±0.2ppm	±0.3ppm	±0.5ppm	±1.0ppm	±2.0ppm		
–20 to 70°C	<b>√</b> **	<b>√</b> **	✓	✓	✓		
–40 to 85°C	_	<b>√</b> **	<b>√</b> **	✓	✓		

# Outline (mm)



Low profile option: 1.4mm max height

# **Test Circuit**



- \* Load 15pF (HCMOS) or  $10k\Omega$  // 10pF (clipped sinewave), inclusive of probe and its capacitance
- and jig capacitance
  \*\* DC cut capacitor required for AC coupled clipped sinewave

# Typical Phase Noise at 14.4MHz

