

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current connector, nom. voltage: 1000 V, nominal current: 125 A, number of connections: 2, connection method: Bolt connection, Rated cross section: 35 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- HFR nut screw locking
- Conical washer CS

Commercial data

Item number	1055643
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE4212
Product key	BE4212
GTIN	4055626693415
Weight per piece (including packing)	79.76 g
Weight per piece (excluding packing)	77.39 g
Customs tariff number	85369010
Country of origin	CN

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Technical data

Product properties

Product type	Bolt connection terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	4.06 W

Connection data

Number of connections per level	2
Nominal cross section	35 mm ²
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal current	125 A
Maximum load current	125 A
Nominal voltage	1000 V
Nominal cross section	35 mm ²
Connection in acc. with standard	NF F61-017
Maximum total current	101 A
Nominal voltage	1000 V
Nominal cross section	25 mm ²

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	2.5 mm ² ... 35 mm ²
Cross section range AWG	14 ... 2 (converted acc. to IEC)
Hole diameter	6.5 mm
Width	15 mm
Bolt length	16 mm
Bolt diameter	6 mm
Screw thread	M6
Tightening torque	8.00 Nm
Connection in acc. with standard	DIN 46235:1983-07
Cross section	6 mm ² ... 35 mm ²
Cross section range AWG	10 ... 2 (converted acc. to IEC)
Hole diameter	6.5 mm

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Width	11 mm
Bolt length	16 mm
Bolt diameter	6 mm
Screw thread	M6
Tightening torque	8.00 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	2.5 mm ² ... 6 mm ²
Cross section range AWG	14 ... 10 (converted acc. to IEC)
Hole diameter	6.5 mm
Width	11 mm
Bolt length	16 mm
Bolt diameter	6 mm
Screw thread	M6
Tightening torque	8.00 Nm
Connection in acc. with standard	NF F00-363:1995-12-01
Cross section	... 25 mm ²
Additional text	The stripping length is based on the specifications of the cable lug manufacturer.
Cross section range AWG	(converted acc. to IEC)
Bolt diameter	6 mm
Screw thread	M6
Tightening torque	8.00 Nm
Connection in acc. with standard	NF F00-363
Cross section	0.5 mm ² ... 25 mm ²
Additional text	Release list on request
Cross section range AWG	(converted acc. to IEC)

Dimensions

Width	16 mm
Height	64 mm
Depth	56.1 mm
Depth on NS 35/7,5	56.1 mm
Depth on NS 35/15	63.6 mm
Bolt length	17 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Result	Test passed
--------	-------------

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 35 mm ²	4.2 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

Result	Test passed
--------	-------------

Test for conductor damage and slackening

Rotation speed	10 (+/- 2) rpm
Revolutions	135
Conductor cross section/weight	35 mm ² / 6.8 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2022-06
Spectrum	Long life test category 2, bogie-mounted

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	$6.12 \text{ (m/s}^2\text{)}^2\text{/Hz}$
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
	NF F61-017

Mounting

Mounting type	NS 35/7,5
	NS 35/15

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Drawings

Circuit diagram



HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1055643>

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group C				
	1000 V	125 A	14 - 1	-
Use group F				
	1000 V	125 A	14 - 1	-
Use group E				
	1000 V	125 A	14 - 1	-

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group C				
	1000 V	125 A	14 - 1	-

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Classifications

ECLASS

ECLASS-11.0	27141120
ECLASS-13.0	27250101

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HV M6/2 NFF - High-current connector



1055643

<https://www.phoenixcontact.com/gb/products/1055643>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk