



M12 FUEL™

M12 FROS5-502X

M12 FUEL™ 150 MM RANDOM ORBITAL SANDER WITH 5.0 MM ORBIT

High performance motor delivers 6,400 to 24,000 sanding strokes per minute for faster material removal

5.0 mm orbit function to deliver efficient body filler removal

Variable speed wheel with 8 speed settings allows the correct speed to be set for different types of material

Compact and ergonomic design for fatigue-free working

Lightweight - only 0.95 kg for the tool and 1.35 kg with a M12™ HIGH OUTPUT™ 5.0 Ah battery

Convenient change of the backing pad by hand without the need for additional tools

The dust port can be mounted on the left or right side and is therefore suitable for both left and right-handed users

Universal hook and loop sanding pad allows easy changing of sanding discs

Vacuum adaptor supplied fits directly to all MILWAUKEE® dust extractors

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



No load speed (rpm)	3,200 - 12,000
Diameter of orbit (mm)	5.0
Sanding pad size (mm)	150
Oscillation rate (opm)	6,400 - 24,000
Weight with battery pack (EPTA) (kg)	1.4 (M12 HB5)
Kit included	2 x M12 HB5 Battery packs, C12 C Charger, HD Box
Article number	4933493651