



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Panel Mount Shroud**

Primary Product Color: **Black**

Primary Product Material: **Thermoplastic**

Number of Positions: **3**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Connector Cover Type	Panel Mount Shroud
----------------------	--------------------

Configuration Features

Number of Rows	1
Number of Positions	3

Body Features

Primary Product Color	Black
Primary Product Material	Thermoplastic

Mechanical Attachment

Mating Alignment Type	Latched
Mating Alignment	With

Dimensions

Product Width	25.15 mm[.99 in]
Product Length	21.21 mm[.83 in]
Product Height	6.35 mm[.25 in]



Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 104503-2
03 MTE PIN HSG SR RIB .100CL

TE Part # 103648-2
03 MTE RCPT HSG SR RIB .100CL

Also in the Series

AMPMODU MTE

Board-to-Board Headers & Receptacles(24)

Connector Caps & Covers(18)

Connector Contacts(27)

Connector Hardware(1)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(444)

Wire-to-Board Connector Assemblies & Housings(298)

Wire-to-Board Headers & Receptacles (420)

Customers Also Bought

TE Part #1-103958-2
10X2 MTE RPT SR LATCH .100CL

TE Part #131250-000
222K132-25/225-0

TE Part #5-104505-3
MTE PIN LP


TE Part #770582-1
14P MINI UMNL PLUG HSG

TE Part #5-104481-6
SHORT POINT RECP CONT LP

TE Part #2195846-8
FPC ANT, MHF4L, 200mm, 698-7125 MHz

TE Part #5-103958-3
5X4 MTE RCPT SR LATCH .100CL

TE Part #211759-1
RECEPT HSG,12 POSN,METRIMATE



Documents

Product Drawings

[03 MTE PANEL MOUNT SR](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_103682-2_N.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_103682-2_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_103682-2_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP MODU MTE Section of Catalog 1307819](#)

English

[AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT](#)

English

[AMPMODU MTE INTERCONNECT SYSTEM](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English