



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Ferrule**

Primary Product Color: **Violet**

Packaging Method: **Carton**

Features

Product Type Features

Strain Relief Accessory Type	Ferrule
------------------------------	---------

Body Features

Primary Product Plating Material	Tin
Primary Product Color	Violet

Dimensions

Compatible Insulation Diameter Range	3.3 – 3.68 mm[.13 – .145 in]
--------------------------------------	------------------------------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in 74018819) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 59500
SAHT TERMASHIELD FERR W/O DIES

Customers Also Bought



TE Part #206499-1
RECEPT ASSY,SZ 1,AMPLIMITE



TE Part #CTJ122E04F-513
MODULE ASSY



TE Part #2174219-1
Push-Pull 7P Plug PS S-Cup Cont KIT/N



TE Part #D12463-000
TTVF050WE-180




TE Part #324056
TERMINAL,T-N R 1/0 1/4



TE Part #590373-000
55/0112-28-9



TE Part #689088-000
S03-04-R



TE Part #169481-2
HTV10 HAND TOOL, TANDEM SPRING



Documents

Product Drawings

[T-SHIELD FERR.,.130-.145](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-327137-2_R.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-327137-2_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-327137-2_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1308940_Sec9_lghlead](#)

English