

Protective Guards without Cover for Grinding

PRODUCT PROPERTIES		ORDERING INFORMATION				
		Diameter mm	Packaging type	Pack quantity	Minimum order quantity	Barcode
Protective guard with clamp fitting, with coding and screw-type fastening						
Suitable for GWS 20-230 (0 601 752 0..); GWS 20-230 H (0 601 850 0..); GWS 20-230 JH (0 601 850 9..); GWS 21-230 HV (0 601 852 B..); GWS 21-230 JHV (0 601 852 3../0 601 852 G..); GWS 22-230 JH (0 601 882 M../0 601 882 Z..); GWS 23-230 / 230 J (0 601 754 0..); GWS 24-230 BV (0 601 854 B..); GWS 24-230 BV + SDS (0 601 854 C..); GWS 24-230 BX + SDS (0 601 864 1..); GWS 24-230 H (0 601 854 4../0 601 884 1../0 601 884 L..); GWS 24-230 JBV (0 601 854 G..); GWS 24-230 JBV + SDS (0 601 854 F..); GWS 24-230 JH (0 601 854 M../0 601 884 2../0 601 884 M..); GWS 24-230 Profi (0 601 854 5..); GWS 25-230 / 230 J (0 601 756 1..); GWS 26-230 B (0 601 856 3../0 601 856 K..); GWS 26-230 BV + SDS (0 601 856 B..); GWS 26-230 JBV (0 601 856 G..); GWS 26-230 JH (0 601 856 4..); GWS 26-230 JH + SDS (0 601 856 5..) Professional; PWS 20-230 (0 603 359 9../0 603 359 W..); PWS 20-230 J (0 603 359 8../0 603 359 V..); PWS 1900 (0 603 359 1..)						
		230	U0	1	1	3165140542173
		2 605 510 298				