

# Product datasheet

Specifications



Floor standing encl. polyester  
vers.PLA compl.sealed  
1500x1250x620 IP65 glazed

NSYPLA15126TG

EAN Code: 3606485434506

## Main

|                           |                                                                      |
|---------------------------|----------------------------------------------------------------------|
| Range                     | PanelSeT                                                             |
| product name              | PanelSeT PLA                                                         |
| Enclosure type            | Multi-purpose                                                        |
| Product or component type | Suitable enclosure                                                   |
| Version                   | PLA                                                                  |
| Nominal height            | 1500 mm                                                              |
| Nominal width             | 1250 mm                                                              |
| Nominal depth             | 620 mm                                                               |
| Enclosure mounting        | Floor-standing                                                       |
| Device composition        | 1 top part<br>1 bottom part<br>2 side part<br>2 door<br>2 rear panel |

## Complementary

|                             |                                                      |
|-----------------------------|------------------------------------------------------|
| Body type                   | Sealed top and bottom part assembled with side parts |
| Door type                   | Transparent front                                    |
| Number of doors             | 2 door(s)                                            |
| Door opening side           | Right and left (120 °)                               |
| Lock type                   | 4 points lock, 5 mm double-bar                       |
| Accessibility for operation | Rear<br>Front                                        |
| Removable parts             | Door by hinges<br>Rear panel by fixing element       |
| Material                    | Polyester reinforced with fibreglass                 |
| Colour                      | Grey (RAL 7035)                                      |
| Standards                   | IEC 62208<br>UL 508 A                                |
| NEMA degree of protection   | NEMA 12<br>NEMA 2<br>NEMA 13<br>NEMA 1               |
| Product certifications      | UL/cUL listed<br>Veritas<br>DNV Marine               |
| Electrical insulation class | Class II                                             |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

|                                     |                                                  |
|-------------------------------------|--------------------------------------------------|
| IP degree of protection             | IP65 conforming to IEC 60529 (completely sealed) |
| IK degree of protection             | IK08 conforming to IEC 62262 (glazed door)       |
| Fire resistance                     | 960 °C conforming to IEC 62208                   |
| Ambient air temperature for storage | -35...90 °C                                      |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 65.000 cm  |
| Package 1 Width              | 128.000 cm |
| Package 1 Length             | 153.000 cm |
| Package 1 Weight             | 97.000 kg  |

## Logistical informations

|                   |    |
|-------------------|----|
| Country of origin | ES |
|-------------------|----|

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

|  Environmental footprint |                                               |
|-----------------------------------------------------------------------------------------------------------|-----------------------------------------------|
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)                                                     | 755                                           |
| Environmental Disclosure                                                                                  | <a href="#">Product Environmental Profile</a> |

Use Better

|  Materials and Substances |                                      |
|------------------------------------------------------------------------------------------------------------|--------------------------------------|
| Packaging made with recycled cardboard                                                                     | No                                   |
| Packaging without single use plastic                                                                       | No                                   |
| SCIP Number                                                                                                | 1341ad4e-77b9-40e3-bab0-32043fbc5959 |

Use Again

|  Repack and remanufacture |                                          |
|--------------------------------------------------------------------------------------------------------------|------------------------------------------|
| Circularity Profile                                                                                          | No need of specific recycling operations |
| Take-back                                                                                                    | No                                       |