



GT-4158

8 analog outputs

0~20 mA

16 bit resolution

Load Resistance: Max 200 Ω

10pt removable terminal block

Facts

General description

Article number	100-8161
Warranty	Up to 2 years
Article status	Active
Shock operating	IEC 60068-2-27 (15G)
Vibration resistance	Sine vibration (based on IEC 60068-2-6), 5 ~ 25 Hz: $\pm 1.6\text{mm}$, 25 ~ 300 Hz: 4G, Sweep rate: 1 octave/min., 20 cycles, Random vibration (based on IEC 60068-2-64), 10 ~ 40 Hz: $0.0125\text{g}^2/\text{Hz}$, 40 ~ 100 Hz: $0.0125 \rightarrow 0.002\text{g}^2/\text{Hz}$, 100 ~ 500 Hz: $0.002 \text{g}^2/\text{Hz}$, 500 ~ 2000 Hz: $0.002 \rightarrow 1.3 \times 10^{-4}\text{g}^2/\text{Hz}$, Test time: 1hrs for each test
Industrial emissions	EN 61000-6-4/A11: 2011
Industrial immunity	EN 61000-6-2: 2019
Installation position	Horisontal, Vertical
Product certifications	CE, UL, cUL, FCC, RoHS, China RoHS, Reach
Power dissipation	Max. 30 mA @ 5 VDC
Isolation	I/O to Logic: Photocoupler isolation, I/O to Field Power: Non-Isolation
Field power	Nominal supply voltage: 24 VDC, Voltage range: 60°C: 18~32 VDC, 70°C: 18~26.4 VDC
Weight	60 g
Module size	12x99x70 mm

Environmental

Mounting	35mm DIN rail
Operating temperature	-20 ~ 60°C
Storage temperature	-40 ~ 85°C
UL temperature	-20 ~ 60°C
Relative humidity	5 ~ 90% non-condensing

Analog output module specifications

Calibration	Not required
Common type	2 common, field power 0 V is common (AGND)
Conversion time	$\leq 0.2 \text{ ms}$, all channels
Data format	16 bit integer (2' compliment)
Diagnostics	Field Power OFF: LED BLINK, Field Power ON: LED OFF (no output), Field Power ON: LED ON (output)
Indicators	8 green output status LEDs
Load resistance	Max. 200 Ω
Module error	$\pm 0.1\%$ full scale @ 25°C, $\pm 0.3\%$ full scale @ -40°C, 70°C
Output format	0 ~ 20 mA
Outputs per module	8 channels single end
Resolution in ranges	16 bit: 0.61 $\mu\text{A}/\text{bit}$

People & Technology. Connected.

We are a people company. Our experienced, skilled and passionate people empower you to meet your challenges through best-in-class, user-friendly solutions. We are a technology company. We help you optimize processes through our software, hardware and services, and through our support. Connecting people and technologies gives you the means to accomplish your goals and ambitions, and gain a competitive edge in today's digitalized world.

Visiting address HQ: Stora Varvsgatan 13a

SE - 211 75 Malmö, SWEDEN

[+46 40 35 86 00 \(tel:+46 40 35 86 00\)](tel:+4640358600)

[info@bejerelectronics.com \(mailto:info@bejerelectronics.com\)](mailto:info@bejerelectronics.com)