

1-1747050-1 ✓ ACTIVE

GRACE INERTIA | GRACE INERTIA 7.92

TE Internal #: 1-1747050-1

2 Position, Plug, Housing, Crimp, Wire-to-Board, Tin (Sn), UL 94V-0,


7.92 mm [.312 in] Centerline, 1 Row, 300 VAC, Wire & Cable,

GRACE INERTIA 7.92

[View on TE.com >](#)



Connectors > Rectangular Connectors > Standard Rectangular Connectors > Glow Wire GRACE INERTIA Plug



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Contact Mating Area Plating Material: **Tin (Sn)**

Contact Retention Within Housing: **With**

[All Glow Wire GRACE INERTIA Plug \(78\)](#)

## Features

### Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	2
Number of Rows	1
Number of Power Positions	2
Number of Signal Positions	2

### Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------



### Body Features

Primary Product Color	Natural
-----------------------	---------

### Contact Features

Multiple Contact Types	Without
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Type	Receptacle
Contact Current Rating (Max)	10 A
Contact Mating Area Plating Material Thickness	.8 $\mu$ m[31.5 $\mu$ in]

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Centerline (Pitch)	7.92 mm[.312 in]
Housing Material	Nylon 6/6 GF

### Dimensions

Wire Size	434.18 – 2723.46 CMA
-----------	----------------------

### Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

### Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)

### Packaging Features

Packaging Quantity	1500
Packaging Method	Bag

## Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



Also in the Series | [GRACE INERTIA 7.92](#)



PCB Headers & Receptacles(21)




Rectangular Connector Housings(18)



Rectangular Power Connectors(39)



Standard Rectangular Connectors(18)




Wire-to-Board Connector Assemblies & Housings(18)




Wire-to-Board Headers & Receptacles (21)

### Customers Also Bought



TE Part #170063-2  
CLUSTER PIN REC



TE Part #171370-5  
CLUSTER BLOCK HSG PBT



TE Part #350561-2  
UMNL PIN 24-18 .0126 AU/BR




TE Part #350767-1  
03P UMNL CAP HSG V0



TE Part #350781-1  
06P UMNL CAP HSG



TE Part #350782-1  
09P UMNL CAP HSG



TE Part #1746972-1  
GRACE INERTIA CONNECTOR 6.2  
MM PITCH REC



TE Part #1747995-1  
GHC EYELET 6.2 3POS PLUG  
HOUSING NATURAL



TE Part #2238007-1  
TERMINAL, PIN, LANCELESS, 22-26  
AWG, EP2



TE Part #5-2295787-7  
STD TIMER PLUG HSG 7P W/EXT.  
LOCKING-SP

### Documents



## Product Drawings

### GIC 7.92 2POS PLUG NAT KEYING B

English

---

## CAD Files

### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1747050-1\\_F.2d\\_dxf.zip](#)

English

### 3D PDF

3D

### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1747050-1\\_F.3d\\_igs.zip](#)

English

### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1747050-1\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Product Specifications

### Application Specification

English