


DRAWING NUMBER C-160.772

DRAWING MADE IN AMERICAN PROJECTION



REV.	DESCRIPTION	DATE	DRAWN	APVD
B1	REVISED PER ECO-10-000444	09JAN10	KK	AEG



FOR .031 TAB-THICKNESS (0.8)

.020 MAX (0.5)

.020 MAX (0.5)



1 FOR USE ON MINIATURE AND STANDARD APPLICATORS

2 FOR USE ON MINIATURE APPLICATORS (AMP-B-MATOR APPLICATION)

3 REELED WITH PAPER LAYER.

4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CUSTOMER COPY FOR REFERENCE ONLY

©1977 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



AMP-HOLLAND N.V.
L'HERYOGHESBOSCH
HOLLAND

4-460772-4	BRASS	TIN
160772-3	BRASS	TIN
4-460772-2	BRASS	TIN
160772-1	BRASS	

WIRE RANGE	INSUL. RANGE	FIRST USED
26-22 AWG 0.12-0.25mm	040-080 DIA.	

ORDER NO.	MATERIAL	PLATING

SCALE	LOC	SIZE	NO	REV
4 ≈ 1	H	A	C-160,772	B1

DR	DATE	DATE
A. BYNEN	14/9-77	24/10/77

NAME 110 Sec FASTON RECEPTACLE

DIMENSIONS IN () INCHES DO NOT SCALE PRINT