
72x72 & 96x96mm Analogue Moving Iron Meters for AC 72x72 & 96x96mm Analogue Moving Coil Meters for DC









- 1 Accessories
- 2 External and Cut-out Dimension
- (3) Connection Diagrams
- 4 Installation
- 1 Accessories: Terminal Cover, Mounting Holders, Screws



③ Connection Diagrams





Specifications:

Standards: IEC51, BS89, DIN 43780, VDE 0410

Enclosure: ABS & Polycarbonate

Base Material UL 94VL

Case & Terminal protection material UL 94VO

Scale division markings DIN 43802

Accuracy: Class 1.5 (+/- 1.5% Maximum error)

Overload: Current 1.2 x In or Un for 2 Hours

10 x In or Un for 5 seconds


Voltage: Current 1.2 x In or Un for 2 Hours

10 x In or Un for 5 seconds


Insulation Test: 2KV 50/60Hz for 1 minute

Temperature: Working temperature -25 - +50 degrees Centigrade

② External and Cut-out Dimensions



4 The meter is fixed in the panel by two screw holders situated on arbitrary opposite corners of the case.



72x72 & 96x96mm Analogue Moving Iron Meters for AC 72x72 & 96x96mm Analogue Moving Coil Meters for DC










- 1 Accessories
- 2) External and Cut-out Dimension
- 3 Connection Diagrams
- 4 Installation

1 Accessories: Terminal Cover, Mounting Holders, Screws



③ Connection Diagrams





Specifications:

Standards: IEC51, BS89, DIN 43780, VDE 0410

Enclosure: ABS & Polycarbonate

Base Material UL 94VL

Case & Terminal protection material UL 94VO

Scale division markings DIN 43802

Accuracy: Class 1.5 (+/- 1.5% Maximum error)

Overload: Current 1.2 x In or Un for 2 Hours

10 x In or Un for 5 seconds


Voltage: Current 1.2 x In or Un for 2 Hours

10 x In or Un for 5 seconds

Insulation Test: 2KV 50/60Hz for 1 minute

Temperature: Working temperature -25 - +50 degrees Centigrade

(2) External and Cut-out Dimensions



4 The meter is fixed in the panel by two screw holders situated on arbitrary opposite corners of the case.

