



Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For service water and process water
- For compressed air (oil purity class 0–3)
- For negative pressure

- For inert gases (e.g. nitrogen)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed up to ø ≤ 54 mm
- Concentric
- Seal ring made of CIIR, black, up to ø ≤ 54 mm

- Seal ring made of EPDM, black, from ø > 54 mm
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material	Cu-DHP copper CW024A (EN 1412)
------------------	--------------------------------

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
62301	12 / 10	15	12	5	3.3
62302	15 / 10	18	12	5.4	3.7
62303	15 / 12	18	15	5.5	3.5
62305	20 / 12	22	15	5.9	3.9

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
62306	20 / 15	22	18	5.7	3.7
62307	25 / 12	28	15	6.6	4.6
62308	25 / 15	28	18	6.4	4.4
62309	25 / 20	28	22	6	3.9
62312	32 / 20	35	22	7.1	5
62313	32 / 25	35	28	6.8	4.5
62316	40 / 20	42	22	8.1	6
62317	40 / 25	42	28	7.9	5.6
62318	40 / 32	42	35	7.6	5
62322	50 / 25	54	28	9.7	7.4
62323	50 / 32	54	35	9.6	7
62324	50 / 40	54	42	9.2	6.1
62325	65 / 25	66.7	28	12	9.7

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
62326	65 / 32	66.7	35	12.1	9.5
62327	65 / 40	66.7	42	12.1	9.1
62328	65 / 50	66.7	54	12.7	9.2
62329	65 / 32	76.1	35	12.6	10
62330	65 / 40	76.1	42	12.6	9.6
62331	65 / 50	76.1	54	14.6	11.1
62332	65 / 65	76.1	66.7	15.1	10.1
62333	80 / 40	88.9	42	14	11
62334	80 / 50	88.9	54	16.2	12.8
62336	80 / 65	88.9	76.1	16.1	10.8
62337	100 / 40	108	42	17.3	14.3
62338	100 / 50	108	54	17.3	13.8
62339	100 / 65	108	66.7	18.9	13.9

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
62340	100 / 65	108	76.1	18.4	13.1
62341	100 / 80	108	88.9	20.3	14.3