

Siemens
EcoTech



SIMATIC ET 200SP HA, terminal block, type P0, 64 push-in terminals, Width: 45 mm



Figure similar

General information	
Product type designation	Type P0
Product function	
• I&M data	Yes
Supply voltage	
Rated value (DC)	24 V
Input current	
Current consumption, max.	640 mA; With one 20 mA encoder supply per channel
Encoder supply	
Number of outputs	32
Output voltage (DC)	24 V
24 V encoder supply	
• Short-circuit protection	Yes; Per output, thermal
• Output current, max.	20 mA; per output
• Output current per module, max.	640 mA
Current carrying capacity	
up to 70 °C, max.	10 A; Permitted load current of the potential group depending on the number of terminal blocks
For process terminals, max.	2 A
Hardware configuration	
Formation of potential groups	
• support of potential groups	Yes
• New potential group	No
• Potential group continued from the left	Yes
Slots	
• Number of slots	1
Potential separation	
between backplane bus and supply voltage	Yes; 3 000 V DC/1 min, type test
between potential groups (power bus)	Yes; 1 500 V DC/1 min, type test (SELV / PELV to functional ground FE)
between process terminals and supply voltage	Yes; 1 500 V DC/1 min, type test
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-40 °C
• horizontal installation, max.	70 °C
• vertical installation, min.	-40 °C

• vertical installation, max.

60 °C

Dimensions

Width	45 mm
Height	175 mm
Depth	77 mm

Weights

Weight, approx.	155 g
-----------------	-------

Classifications

	Version	Classification
eClass	14	27-24-26-07
eClass	12	27-24-26-07
eClass	9.1	27-24-26-07
eClass	9	27-24-26-07
eClass	8	27-24-26-07
eClass	7.1	27-24-26-07
eClass	6	27-24-26-07
ETIM	10	EC001603
ETIM	9	EC001603
ETIM	8	EC001603
ETIM	7	EC001603

Approvals / Certificates

General Product Approval



[Miscellaneous](#)



[China RoHS](#)



General Product Approval

For use in hazardous locations



[Declaration of Conformity](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)



Maritime application

Environment



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



last modified:

10/23/2025