

Parker Product Datasheet



The main function of Ermeto DIN male stud high pressure hydraulic tube fittings is to connect different numbers of tubes and hoses. This broad range of fittings is available in steel and in stainless steel.

PART NUMBER: EGE20SR1EDCF
SHAPE: Straight
CONNECTION 1 TYPE: Male 24° Cone (with O-Ring)
CONNECTION 1 SIZE: 20 mm (O.D.)
OPTIONAL ACCESSORIES: n/a
SEAL MATERIAL: NBR
BODY MATERIAL: Steel
CONNECTION 2 SIZE: G 1 A
CONNECTION 2 TYPE: Male BSPP
PRODUCT SERIES: EO Heavy

PRODUCT OVERVIEW

The main function of Ermeto DIN male stud high pressure hydraulic tube fittings is to connect different numbers of tubes or hoses. This broad range of fittings, types GEO, GE-M-ED, GE-R-ED up to GE-M is available in steel and in a stainless steel version. Depending on the specific application, these fittings can be delivered with cutting ring (EO-PSR or DPR) or elastomeric seal (EO-2).

Markets:

- Automotive
- Defence
- Energy

- Environment
- Industrial
- Infrastructure
- Machine Tools
- Materials Handling
- Mobile
- Oil and Gas
- Power Generation
- Process
- Transportation
- Water

Applications:

- Suitable for general hydraulic applications.

Features/ benefits:

- Steel and Stainless steel fittings have a high corrosion resistance to aggressive media and environmental influences. These features extend the range of applications.
- High pressure: Ermeto DIN male stud high pressure hydraulic tube fittings have pressure ratings of up to 800 bar (S series) and 500 bar (L series), so that the fittings can be used in a wide range of applications.

TECH SPECIFICATIONS

CONNECTION 2 TYPE	Male
CONFIGURATION	Swivel to Port
APPLICATION	Chemical Transfer
FOR FLUID TYPE	Steam
INDUSTRY	Transportation
APPLICATION	Mobile Hydraulics
FOR FLUID TYPE	Chemicals
PRODUCT SERIES	EO Heavy
INDUSTRY	Marine
APPLICATION	Fuel Transfer

INDUSTRY	Agriculture
MINIMUM AMBIENT TEMPERATURE	-50 °C
SHAPE	Straight
SEAL TYPE	ED Seal
FOR FLUID TYPE	Fuels
INDUSTRY	Industrial Manufacturing Equipment
APPLICATION	Hydraulics
CONNECTION 1 TYPE	24° Cone (with O-Ring)
FOR FLUID TYPE	Hydraulic Fluids
FOR FLUID TYPE	Gases
INDUSTRY	Material Handling
APPLICATION	Oilfield
CONNECTION 2 TYPE	BSPP (ISO 1179)
INDUSTRY	Automotive
CONNECTION 1 TYPE	Male
MAXIMUM OPERATING PRESSURE	420 bar
APPLICATION	Packaging
PRODUCT STYLE	Adjustable Position
MAXIMUM AMBIENT TEMPERATURE	248 °F
SEAL MATERIAL	NBR
PRODUCT TYPE	Hydraulic DIN Fittings
SPECIFICATIONS MET	ISO 1179
DIVISION	High Pressure Connectors Europe Division
MINIMUM FLUID TEMPERATURE	-58 °F
MAXIMUM FLUID TEMPERATURE	248 °F
TECHNOLOGY	Fluid & Gas Handling

DIVISION	High Pressure Connectors Europe Division
CONNECTION 2 SIZE	G 1 A inch Thread
MAXIMUM FLUID TEMPERATURE	120 °C
ACCESSORIES INCLUDED	n/a
CONNECTION 1 SIZE	20 mm Tube O.D.
MINIMUM FLUID TEMPERATURE	-50 °C
BODY MATERIAL	Steel
MAXIMUM AMBIENT TEMPERATURE	120 °C
INDUSTRY	Construction
MINIMUM AMBIENT TEMPERATURE	-58 °F
BRAND	Ermeto