


SKINTOP® PG nickel-plated brass cable glands • Easy to install



SKINTOP® MS / SKINTOP® MSR



Benefits

- Maximum reliability
- Optimum strain relief
- Wide, variable clamping ranges

Application range

SKINTOP® MS

- In areas where mechanical and chemical stability are critical
- Chemical industry
- Measurement and control technology
- Machine and equipment manufacturing
- Plant engineering

SKINTOP® MSR

- With reducing seal insert, to seal cables with smaller outer diameters.

Product Make-up

- PG connection thread

Note

- Counter nut to be used: SKINDICHT® SM
- Refer to SKINTOP® PG accessories for suitable accessories

Technical data



Classification

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description:
Cable screw gland



Caution

Refer to Appendix T21 for the installation dimensions and torques



Material

Body: nickel-plated brass
Insert: polyamide
Sealing ring: CR
O-ring: NBR



Protection rating

IP 68 - 10 bar



Temperature range

dynamic -25 °C up to + 100 °C
static -40 °C up to +100 °C

Article number	Article designation / size	Clamping range ØF (mm)	SW wrench size mm	Overall length, C (mm)	Thread length, D (mm)	Pieces / PU
SKINTOP® MS						
52015700	MS 7	2 - 6.5	14	25.0	5	100
52015710	MS 9	4 - 8	17	29.0	6	100
52015720	MS 11	4 - 10	20	32.0	6	50
52015730	MS 13,5	5 - 12	22	34.0	6.5	50
52015740	MS 16	8 - 14	24	35.0	6.5	50
52015750	MS 21	11 - 18	30	40.0	7	25
52015760	MS 29	16 - 25	40	48.0	8	25
52015765	MS 36	19 - 32	50	62.0	15	10
52015766	MS 42	28 - 38	57	62.0	15	5
52015767	MS 48	34 - 44	64	62.0	15	5
SKINTOP® MSR						
52015770	MSR 7	2 - 5	14	25.0	5	100
52015780	MSR 9	2 - 6	17	29.0	6	100
52015790	MSR 11	3 - 7	20	32.0	6	50
52015800	MSR 13,5	4 - 9	22	34.0	6.5	50
52015810	MSR 16	6 - 13	24	35.0	6.5	50
52015820	MSR 21	8 - 16	30	40.0	7	25
52015830	MSR 29	10.5 - 20	40	48.0	8	25
52015831	MSR 36	19 - 26	50	62.0	15	10
52015832	MSR 42	24 - 31	57	62.0	15	5
52015833	MSR 48	28 - 35	64	62.0	15	5

Photographs are not to scale and do not represent detailed images of the respective products.