

# Product data sheet

## Automation technology - Data transmission




|                     |  |
|---------------------|--|
| Product description | <b>M12 Male cable connector, Contacts: 4, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238</b> |
| Area                | <b>M12-D</b>   |
| Coding              | <b>D-coded</b>   |
| Series              | <b>825</b>   |
| Part no.            | <b>99 3729 810 04</b>  |


### Illustration



### Scale drawing



### Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

## Technical data

### General features

|                           |                                    |
|---------------------------|------------------------------------|
| Part no.                  | <b>99 3729 810 04</b>              |
| Connector design          | Male cable connector               |
| Type standard             | DIN EN 61076-2-101                 |
| Coding                    | D-coded                            |
| Version                   | Connector pin straight             |
| Connector locking system  | screw                              |
| Termination               | screw clamp                        |
| Degree of protection      | IP67                               |
| Connection cross-section  | max. 0.75 mm <sup>2</sup> / AWG 18 |
| Cable outlet              | 6.0-8.0 mm                         |
| Temperature range from/to | -40 °C / 85 °C                     |
| Mechanical operation      | > 100 Mating cycles                |
| Weight (g)                | 42.87                              |
| Customs tariff number     | 85369010                           |
| Country of Origin         | HU                                 |

### Electrical parameters

|                           |                      |
|---------------------------|----------------------|
| Rated voltage             | 250 V                |
| Rated impulse voltage     | 2500 V               |
| Rated current             | 4.0 A                |
| Insulation resistance     | ≥ 10 <sup>10</sup> Ω |
| Pollution degree          | 3                    |
| Transmission rate         | CAT 5                |
| Overvoltage category      | II                   |
| Insulating material group | III                  |

# Product data sheet

## Automation technology - Data transmission



|                     |  |
|---------------------|--|
| Product description | <b>M12 Male cable connector, Contacts: 4, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238</b> |
| Area                | <b>M12-D</b>   |
| Coding              | <b>D-coded</b>   |
| Series              | <b>825</b>   |
| Part no.            | <b>99 3729 810 04</b>  |

|                   |                |
|-------------------|----------------|
| EMC compliance    | shieldable     |
| Shield connection | Shielding ring |
| Voltage           | 1400 V DC      |

### Material

|                       |                                      |
|-----------------------|--------------------------------------|
| Housing material      | Zinc die-cast nickel-plated          |
| Contact body material | PA                                   |
| Contact material      | CuZn (brass)                         |
| Contact plating       | Au (gold)                            |
| Locking material      | Zinc die-cast nickel-plated          |
| REACH SVHC            | CAS 7439-92-1 (Lead)                 |
| SCIP number           | da24e527-8dc9-4c4c-a6a6-8c94b3e78a27 |

### Authorization/approvals

|           |         |
|-----------|---------|
| Approvals | UL 2238 |
|-----------|---------|

### Classifications

|             |             |
|-------------|-------------|
| eCl@ss 11.1 | 27-44-01-02 |
| ETIM 9.0    | EC002635    |

### Declarations of conformity

|                       |   |
|-----------------------|---|
| Low Voltage Directive | 2014/35/EU (EN 60529:1991   2014/35/EU;EN 60204-1:2018) |
|-----------------------|---|

### Assembly instructions

1. Bead pressing screw, pinch ring, seal and shielding ring to cable.
2. Dismantle cable.
3. Strip single wires, shorten shield and revert to shielding ring.
4. Thread single wires through sleeve, mount shielding ring, seal and pinch ring. Slightly tighten pressing screw to fix the cable.
5. Screw on single wires (0.4 Nm).
6. Screw sleeve to male/female insert.
7. Tighten pressing screw.

The diagram shows the following components and steps:

- female insert assembled** and **male insert assembled** are shown on the left.
- The main assembly shows a cable with a **strip** of length 5 and a **shield** of length 6.
- Labels include: **35 dismantle**, **shielding ring**, **pinch ring**, **seal**, **pressing screw**, and **sleeve with insulating sleeve**.
- Torque specifications: **0.8-1.0 Nm** for the pressing screw and **1.0 Nm** for the sleeve.
- A note says: **shorten shield and revert to shielding ring**.

## Product data sheet

# Automation technology - Data transmission



|                     |  |
|---------------------|--|
| Product description | <b>M12 Male cable connector, Contacts: 4, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238</b> |
| Area                | <b>M12-D</b>   |
| Coding              | <b>D-coded</b>   |
| Series              | <b>825</b>   |
| Part no.            | <b>99 3729 810 04</b>  |

### General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).