


SV7051



Vortex flow meter

SVR11XGXD0KG/US



Product characteristics		
Number of inputs and outputs	Number of analogue outputs: 1	
Measuring range	5...85 l/min	0.265...4.509 m/s
Process connection	threaded connection G 1 external thread DN20	
Application		
Special feature	Gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Application	for industrial applications	
Installation	connection to pipe by means of an adapter	
Media	ultra-pure water; water	
Medium temperature [°C]	0...125	
Min. bursting pressure	10 bar	1 MPa
Note on min. burst pressure	125 °C	
Pressure rating	16 bar	1.6 MPa



Vortex flow meter

SVR11XGXD0KG/US

Note on pressure rating	≤ 90 °C	
Electrical data		
Operating voltage [V]	8...33 DC	
Current consumption [mA]	< 5	
Min. insulation resistance [MΩ]	100; (500 V DC)	
Protection class	III	
Power-on delay time [s]	< 2	
Measuring principle	Vortex	
Inputs / outputs		
Number of inputs and outputs	Number of analogue outputs: 1	
Outputs		
Total number of outputs	1	
Output signal	analogue signal	
Number of analogue outputs	1	
Analogue current output [mA]	4...20; (Q [l/min] = 5,313 x (I - 4 mA))	
Max. load [Ω]	< (Ub - 8 V) / 20 mA; Ub = 24 V: 800	
Measuring/setting range		
Measuring range	5...85 l/min	0.265...4.509 m/s
Temperature monitoring		
Internal heating temperature probe	1 K/mW	
Measuring range [°C]	0...125	
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)	Q < 50 % MEW: < 1 % MEW / Q > 50 % MEW: < 2 % MW; (water)	
Repeatability	0,2; (% of the final value)	
Temperature monitoring		
Accuracy [K]	± 0,3 ± 0,005 x T	
Response times		
Flow monitoring		
Response time [s]	0.37; (T09)	
Temperature monitoring		
Dynamic response T05 / T09 [s]	< 10 / < 30	
Operating conditions		
Ambient temperature [°C]	-15...85	
Note on ambient temperature	Medium temperature > 0 °C: -40...85	
Storage temperature [°C]	-40...85	
Protection	IP 65	
Cavitation	P(absolute) discharge / P(difference) > 5.5 to avoid cavitation	
Tests / approvals		
EMC	EN IEC 61326-1:2021	
Shock resistance	DIN EN 60068-2-27	30 g (11 ms)

SV7051



Vortex flow meter

SVR11XGXD0KG/US

Vibration resistance	DIN EN 60068-2-6	with water / 10...61 Hz 1 mm
		with water / 61...2000 Hz 2 g
MTTF [years]	395.9	
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]	115.2	
Housing	rectangular	
Dimensions [mm]	105 x 30.2 x 61.1	
Materials	Housing: PPS 40% glass fibre; electronics: PC 10% glass fibre	
Materials (wetted parts)	sensor: PPSU; Pipe section: PPS 40% glass fibre; Sealing: FKM	
Tightening torque [Nm]	12	
Process connection	threaded connection G 1 external thread DN20	

Displays / operating elements		
Display		colour display 1,44", 128 x 128 pixels
		2 x LED, yellow

Remarks		
Remarks	MW = measured value	
	MEW = Final value of the measuring range	
Pack quantity	1 pcs.	

Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



Vortex flow meter

SVR11XGXD0KG/US

Connection



OUT: analogue output

T1 / T2: Pt1000


colours to DIN EN 60947-5-2

Core colours :

BK = black
 BN = brown
 BU = blue
 WH = white

Diagrams and graphs

pressure rating curve



P [bar] = pressure

T [°C] = temperature

1 = permanent


SV7051

Vortex flow meter

SVR11XGXD0KG/US



Pressure loss



dP [mbar] = Pressure loss

Q [l/min] = volumetric flow quantity