





D

C

B

A



RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

.068	1.73	1.000	25.40
.065	1.65	.700	17.78
.063	1.60	.450	11.43
.060	1.52	.425	10.80
.045	1.14	.400	10.16
.030	0.76	.300	7.62
.015	0.38	.180	4.57
.012	0.30	.175	4.45
.010	0.25	.156	3.96
.008	0.20	.125	3.18
.005	0.13	.078	1.98
.003	0.08	.073	1.85
.001	0.03	.070	1.78
[IN]	MM	[IN]	MM

CONVERSION TABLE

- 1 POST TO WITHSTAND 13 NEWTONS (3LBS.) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2 TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3 MEASURED AT SURFACE -A-
- 4 PLASTIC FLASH PERMITTED IN THIS AREA.
- 5 PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- 6 ONE HOLE MAY BE UNDERSIZED (.065/.060 DIA.) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7 MATERIAL: HEADER-THERMOPLASTIC POLYESTER
GLASS-FILLED 94V-0 (NATURAL)
POST-COPPER ALLOY (TIN PLATED)
- 8 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 9 PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10 POST TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11 POST MUST WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12 DIMENSION SHOULD BE .175 MIN WHEN MATING WITH A MTA-156 CONNECTOR ASSEMBLY OR A SL-156 CONNECTOR ASSEMBLY.
- 13 PIN BURR OF .005 MAX. VERTICAL AND .003 MAX. HORIZONTAL PERMITTED AT POST TIPS ON BOTH ENDS.
- 14 SPECIAL PACKAGING VARIATION FOR IMPROVED PRODUCT PROTECTION.

31.70	1.248	8	3-640445-8	4
95.10	3.744	24	2-640445-4	
91.14	3.588	23	2-640445-3	
87.17	3.432	22	2-640445-2	
83.21	3.276	21	2-640445-1	
79.25	3.120	20	2-640445-0	
75.29	2.964	19	1-640445-9	
71.32	2.808	18	1-640445-8	
67.36	2.652	17	1-640445-7	
63.40	2.496	16	1-640445-6	
59.44	2.340	15	1-640445-5	
55.47	2.184	14	1-640445-4	
51.51	2.028	13	1-640445-3	
47.55	1.872	12	1-640445-2	
43.59	1.716	11	1-640445-1	
39.62	1.560	10	1-640445-0	
35.66	1.404	9	640445-9	
31.70	1.248	8	640445-8	
27.74	1.092	7	640445-7	
23.77	.936	6	640445-6	
19.81	.780	5	640445-5	
15.85	.624	4	640445-4	
11.89	.468	3	640445-3	
7.92	.312	2	640445-2	
MM	[IN]	2	640445-2	
L		NUMBER OF POSITIONS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. HOOVER
CHK
D. BOSSI
APVD
D. BOSSI
PRODUCT SPEC

05-NOV-2002
05-NOV-2002
05-NOV-2002

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

WEIGHT

CUSTOMER DRAWING

NAME

MTA-156 HEADER ASSEMBLY,
FRICTION LOCK, STRAIGHT
.045 SQUARE POST, TIN PLATED

SIZE
A1

SCALE
5:1

SHEET
1 OF 1

REV
AD1

TE Connectivity

RESTRICTED TO