

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : 8461 - VERNIS V991
Product code : 008461
Type of product : Varnish,Aerosol.
Vaporizer : Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Industrial/Professional use spec : Industrial
For professional use only

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

ITW Spraytec
42, rue Gallieni
F-92600 Asnières sur Seine - France
T +33(0)1.40.80.32.32 - F +33(0)1.40.80.32.30
infofds@itwpc.com - www.jelt.fr

1.4. Emergency telephone number

Emergency number : FRANCE :+ 33 (0)1 45 42 59 59

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol, Category 1 H222;H229
Serious eye damage/eye irritation, Category 2 H319
Specific target organ toxicity — Single exposure, Category 3, Narcosis H336
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS02

GHS07

Signal word (CLP) : Danger
Hazardous ingredients : Acetone
Hazard statements (CLP) : H222 - Extremely flammable aerosol.
H229 - Pressurised container: May burst if heated.
H319 - Causes serious eye irritation.
H336 - May cause drowsiness or dizziness.
Precautionary statements (CLP) : P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
No smoking.
P211 - Do not spray on an open flame or other ignition source.
P251 - Do not pierce or burn, even after use.
P261 - Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 - Use only outdoors or in a well-ventilated area.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P102 - Keep out of reach of children.
EUH-statements : EUH066 - Repeated exposure may cause skin dryness or cracking.

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
butane	(CAS-No.) 106-97-8 (EC-No.) 203-448-7	20 - 40	Flam. Gas 1, H220 Press. Gas (Liq.), H280
Acetone	(CAS-No.) 67-64-1 (EC-No.) 200-662-2 (EC Index-No.) 606-001-00-8 (REACH-no) 01-2119471330-49	20 - 40	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
Propane	(CAS-No.) 74-98-6 (EC-No.) 200-827-9 (REACH-no) 01-2119486944-21	< 20	Flam. Gas 1, H220 Press. Gas (Liq.), H280
xylene	(CAS-No.) 1330-20-7 (EC-No.) 215-535-7 (EC Index-No.) 601-022-00-9 (REACH-no) 01-2119488216-32	< 10	Flam. Liq. 3, H226 Acute Tox. 4 (Dermal), H312 Acute Tox. 4 (Inhalation), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319 STOT SE 3, H335 STOT RE 2, H373 Asp. Tox. 1, H304 Aquatic Chronic 3, H412
ethylbenzene	(CAS-No.) 100-41-4 (EC-No.) 202-849-4 (EC Index-No.) 601-023-00-4	< 5	Flam. Liq. 2, H225 Acute Tox. 4 (Inhalation), H332 STOT RE 2, H373 Asp. Tox. 1, H304
2,5 thiophenediylbis(5-tert-butyl-1,3-benzoxazole)	(CAS-No.) 7128-64-5	< 1	Aquatic Chronic 4, H413

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Call a POISON CENTER/doctor/physician if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Call a POISON CENTER/doctor/physician if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: May cause drowsiness or dizziness.
Symptoms/effects after eye contact	: Eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water haze. Carbon dioxide. Foam.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Fire hazard	: Extremely flammable aerosol.
Explosion hazard	: Pressurised container: May burst if heated.
Hazardous decomposition products in case of fire	: Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

5.3. Advice for firefighters

Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.
--------------------------------	--

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

No additional information available

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Mechanically recover the product.

Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Use only outdoors or in a well-ventilated area. Avoid breathing dust/fume/gas/mist/vapours/spray. Avoid contact with skin and eyes. Wear personal protective equipment.

Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Keep cool.

Incompatible materials : Heat sources. Direct sunlight. Sources of ignition.

Storage temperature : < 50 °C

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Acetone (67-64-1)

France - Occupational Exposure Limits

Local name	Acétone
VME (mg/m ³)	1210 mg/m ³
VME (ppm)	500 ppm
VLE (mg/m ³)	2420 mg/m ³
VLE (ppm)	1000 ppm

United Kingdom - Occupational Exposure Limits

Local name	Acetone
WEL TWA (mg/m ³)	1210 mg/m ³
WEL TWA (ppm)	500 ppm
WEL STEL (mg/m ³)	3620 mg/m ³
WEL STEL (ppm)	1500 ppm

butane (106-97-8)

France - Occupational Exposure Limits

Local name	n-Butane
VME (mg/m ³)	1900 mg/m ³
VME (ppm)	800 ppm

United Kingdom - Occupational Exposure Limits

Local name	Butane
------------	--------

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

WEL TWA (mg/m ³)	1450 mg/m ³
WEL TWA (ppm)	600 ppm
WEL STEL (mg/m ³)	1810 mg/m ³
WEL STEL (ppm)	750 ppm
Remark (WEL)	Carc, (only applies if Butane contains more than 0.1% of buta-1,3-diene)

xylene (1330-20-7)

France - Occupational Exposure Limits

Local name	Xylène, isomères mixtes, purs
VME (mg/m ³)	221 mg/m ³
VME (ppm)	50 ppm
VLE (mg/m ³)	442 mg/m ³
VLE (ppm)	100 ppm

United Kingdom - Occupational Exposure Limits

Local name	Xylene, o-,m-,p- or mixed isomers
WEL TWA (mg/m ³)	220 mg/m ³
WEL TWA (ppm)	50 ppm
WEL STEL (mg/m ³)	441 mg/m ³
WEL STEL (ppm)	100 ppm
Remark (WEL)	Sk, BMGV

ethylbenzene (100-41-4)

United Kingdom - Occupational Exposure Limits

Local name	Ethylbenzene
WEL TWA (mg/m ³)	441 mg/m ³
WEL TWA (ppm)	100 ppm
WEL STEL (mg/m ³)	552 mg/m ³
WEL STEL (ppm)	125 ppm
Remark (WEL)	Sk

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Materials for protective clothing:

Wear suitable protective clothing

Hand protection:

In case of repeated or prolonged contact wear gloves. Chemical resistant gloves (according to European standard NF EN 374 or equivalent). The choice of appropriate gloves depends not only on the material, but also on other quality criteria that may vary from one manufacturer to another. As the product is a preparation made from several substances, glove material resistance may not be calculated in advance and must be tested before use. The exact penetration time of glove material is to be determined by the manufacturer of protective gloves and respected.

Eye protection:

Safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

Environmental exposure controls:

Avoid release to the environment.

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Organic solvent.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: < 0 °C
Flash point	: < 0 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: 0,854 g/cm ³
Solubility	: insoluble in water. soluble in most organic solvents.
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Pressurised container: May burst if heated.
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Extremely flammable aerosol. Pressurised container: May burst if heated.

10.2. Chemical stability

Extremely flammable aerosol. Heating may cause a fire or explosion. Stable under normal conditions.

10.3. Possibility of hazardous reactions

None under normal conditions.

10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

Acetone (67-64-1)

LD50 oral rat	5800 mg/kg
LD50 dermal rabbit	> 15800 mg/kg
LC50 inhalation rat (mg/l)	≈ 76 mg/l/4h
Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

STOT-single exposure	: May cause drowsiness or dizziness.
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

8461 - VERNIS V991

Vaporizer	Aerosol
-----------	---------

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Acute aquatic toxicity	: Not classified
Chronic aquatic toxicity	: Not classified

Acetone (67-64-1)

LC50 fish 1	5540 - 11000 mg/l
EC50 Daphnia 1	8800 mg/l
NOEC chronic algae	430 mg/l

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

Acetone (67-64-1)

Log Kow	-0,24
---------	-------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available




SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations	: Dispose in a safe manner in accordance with local/national regulations. Container under pressure. Do not drill or burn even after use.
--	--

SECTION 14: Transport information

In accordance with ADR / IATA / IMDG

ADR	IMDG	IATA
14.1. UN number		
UN 1950	UN 1950	UN 1950
14.2. UN proper shipping name		
AEROSOLS	AEROSOLS	Aerosols, flammable
Transport document description		
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1	UN 1950 Aerosols, flammable, 2.1
14.3. Transport hazard class(es)		
2.1	2.1	2.1
		
14.4. Packing group		
Not applicable	Not applicable	Not applicable

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.5. Environmental hazards

Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No
------------------------------------	---	------------------------------------

No supplementary information available

14.6. Special precautions for user

Overland transport

Classification code (ADR)	: 5F
Special provisions (ADR)	: 190, 327, 344, 625
Limited quantities (ADR)	: 1I
Excepted quantities (ADR)	: E0
Packing instructions (ADR)	: P207
Special packing provisions (ADR)	: PP87, RR6, L2
Mixed packing provisions (ADR)	: MP9
Transport category (ADR)	: 2
Special provisions for carriage - Packages (ADR)	: V14
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV9, CV12
Special provisions for carriage - Operation (ADR)	: S2
Tunnel restriction code (ADR)	: D

Transport by sea

Special provisions (IMDG)	: 63, 190, 277, 327, 344, 381, 959
Packing instructions (IMDG)	: P207, LP200
Special packing provisions (IMDG)	: PP87, L2
EmS-No. (Fire)	: F-D
EmS-No. (Spillage)	: S-U
Stowage category (IMDG)	: None
Stowage and handling (IMDG)	: SW1, SW22
Segregation (IMDG)	: SG69

Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg
CAO packing instructions (IATA)	: 203
CAO max net quantity (IATA)	: 150kg
Special provisions (IATA)	: A145, A167, A802
ERG code (IATA)	: 10L

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to REGULATION (EU) No 649/2012 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 4 July 2012 concerning the export and import of hazardous chemicals.

Substance(s) are not subject to Regulation (EC) No 850/2004 of the European Parliament and of the Council of 29 April 2004 on persistent organic pollutants and amending Directive 79/117/EEC.

15.1.2. National regulations

France

Occupational diseases	: RG 4 BIS - Affections gastro-intestinales provoquées par le benzène, le toluène, les xylènes et tous les produits en renfermant RG 84 - Affections engendrées par les solvants organiques liquides à usage professionnel
-----------------------	---

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Germany

Reference to AwSV : Water hazard class (WGK) 2, Significantly hazardous to water (Classification according to AwSV, Annex 1)

12th Ordinance Implementing the Federal Immission Control Act - 12.BImSchV : Is not subject of the 12. BImSchV (Hazardous Incident Ordinance)

Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed

SZW-lijst van mutagene stoffen : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Borstvoeding : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Vruchtbaarheid : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : xylene is listed

Denmark

Class for fire hazard : Class I-1

Store unit : 1 liter

Classification remarks : F+ <Aerosol 1>; Emergency management guidelines for the storage of flammable liquids must be followed

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product
Pregnant/breastfeeding women working with the product must not be in direct contact with the product

15.2. Chemical safety assessment

No additional information available

SECTION 16: Other information

Full text of H- and EUH-statements:	
Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Aquatic Chronic 4	Hazardous to the aquatic environment — Chronic Hazard, Category 4
Asp. Tox. 1	Aspiration hazard, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Gas 1	Flammable gases, Category 1
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Press. Gas (Liq.)	Gases under pressure : Liquefied gas
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT RE 2	Specific target organ toxicity — Repeated exposure, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H319	Causes serious eye irritation.

8461 - VERNIS V991

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

H332	Harmful if inhaled.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H373	May cause damage to organs through prolonged or repeated exposure.
H412	Harmful to aquatic life with long lasting effects.
H413	May cause long lasting harmful effects to aquatic life.
EUH066	Repeated exposure may cause skin dryness or cracking.

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.