




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **3**
Terminal Orientation: **Straight**
Primary Product Color: **Natural**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
------------------	------



Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Polyamide
Dimensions	
Product Length	20.4 mm[.803 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Packaging Features	
Packaging Quantity	2000
Packaging Method	Carton

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 925015-1
FF 110 REC HSG 3P NYLON BLACK



TE Part # 925306-2
FF 312 REC HSG 3P NYLON CLEAR



TE Part # 170258-1
FF 250 REC 14-12AWG BR REREELING




TE Part # 150653-1
FF 312 REC HSG 3P NYLON BLACK




TE Part # 626213-1
FASTIN-ON 0.312 FLAG REC NYLON 6.6



TE Part # 925176-5
FF 312 3P HOUSING REC POLYAMID 6.6 BLACK



TE Part # 170258-2
FF 250 REC 14-12AWG TPBR REREELING




TE Part # 925475-1
FF 110 REC HSG 3P NYLON NAT



TE Part # 927284-2
FF 250 REC HSG 3P NYLON NAT




TE Part # 1-172131-1
FF 250 CAP HSG 3P NYLON NAT



TE Part # 626213-2
3 CIR FASTIN-ON RECP HSG PRETO

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(195)




Insertion & Extraction Tools(2)




Quick Disconnects(216)

Customers Also Bought




TE Part #282108-1
AMP SUPERSEAL 1.5 SERIES 6P CA



TE Part #282375-1
070 MULTILOCK RCPT CONT



TE Part #175022-1
250 PL EX REC. 18-14AWG PTBR



TE Part #3-350566-1
MINI AMP-IN 22-18 PTLP/PHBZ






TE Part #280095-2
FF 250 REC 0.3-0.8MM2 PTBR




TE Part #1-962915-1
TAB 2.8x0.8 CONTACT CS SWS Sn




TE Part #180453-2
FF 312 REC 1-2.5MM2 TPBR



TE Part #926883-1
UNIVERSAL M-N-L PIN



TE Part #927689-3
26P MOD4 ABDECKKAPP



TE Part #1544453-1
LANG.A.SERT 8 BOIT

Documents

Product Drawings

FF 250 REC HSG 3P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_180913_AW.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_180913_AW.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_180913_AW.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English