

PRODUCT DATASHEET

SL FLEX LA RW35ST P 158W 730 WAL

STREETLIGHT FLEX LARGE RW35ST | Light distribution optimized for wider roads and area lighting



Areas of application

- Outdoor use (IP66)
- M-, C- and P-class roads acc. to EN 13201
- Parking
- Public areas
- Industry

Product benefits

- Durable design and highest quality component selection for long lasting performance
- Quick and easy wiring, due to tool-free housing opening and push button terminal
- High light uniformity
- 3 light colors available, perfectly suited to illuminate highly diverse surroundings
- No upper light output ratio (ULOR 0%) when mounted at 0° tilt
- Automatic mains disconnection when opening the housing
- 5 years guarantee

Product features

- Light distribution with great depth
- Very long lifetime (L90/B10): Up to 100,000 h (at 25 °C)
- Spigot included, suitable for 48...60 mm diameter poles
- Adjustable spigot for both side-entry and post-top installation
- +/- 15° tilt angle adjustment without opening the housing
- High luminous efficacy: up to 151 lm/W



- Operating temperature: -40...50 °C
- High surge protection: up to 10 kV (L/N-GND)
- Push fit terminal for a quick and easy electrical connection
- Protection class: II


TECHNICAL DATA

Electrical data

Nominal wattage	158.00 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	756 mA
Inrush current	80 A
Inrush current time T_{h50}	150 μ s
Max. no. of lum. on circuit break. B16 A	7
Max. no. of lum. on circuit break. C10 A	8
Max. no. of lum. on circuit break. C16 A	14
Power factor λ	> 0.90
Total harmonic distortion	< 10 %
Protection class	II
Operating mode	Integrated LED driver

Photometrical data

Luminous flux	23200 lm
Luminous efficacy	147 lm/W
Color temperature	3000 K
Light color (designation)	Warm White
Color rendering index Ra	70
Standard deviation of color matching	< 5 sdc _m
Low flicker	Yes
Photobiological safety group acc. to EN62778	RG1
Photobiological safety group acc. to EN62471	RG1
Beam angle	35 ° x 135 °



Dimensions & Weight

Length	617.00 mm
Width	300.00 mm
Height	90.00 mm
Product weight	7700.00 g

Materials & Colors

Product color	White aluminum
Housing color	White aluminum
Body material	Aluminum
Cover material	Tempered glass
Light emitting surface material	Glass
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-40...+50 °C
Temperature range at storage	-30...+80 °C
Type of connection	Screwless terminal
Type of protection	IP66
Protection class IK (shock resistance)	IK08

Dimmable	No
Mounting type	Post top
Mounting location	Pole
Adjustable	Yes
LED module replaceable	Not replaceable

Lifespan

Lifespan L70/B50 at 25 °C	100000 h
Lifespan L80/B10 at 25 °C	100000 h
Lifespan L90/B10 at 25 °C	100000 h
Number of switching cycles	100000

Control gear

ECG - Output ripple current	≤ 10 %
-----------------------------	--------

Certificates & Standards

Standards	CE / ENEC / EAC
Luminaire with limited surface temperature, "D sign"	No
Ball shot safe	No





Additional product data

Product remark	Available from September 2021
----------------	-------------------------------

EQUIPMENT / ACCESSORIES

- Spigot for 42 and 76 mm poles available separately

DOWNLOAD DATA

DOWNLOAD DATA	
	User instruction STREETLIGHT FLEX
	Declarations of conformity SL FLEX MD
	IES file (IES) SL FLEX LA P 158W 730 RW35ST WAL
	LDT file (Eulumdat) SL FLEX LA P 158W 730 RW35ST WAL

DOWNLOAD DATA



R3D file (Relux 3D Model)
SL FLEX LA



M3D file (3D Model)
SL FLEX LA

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075552500	Shipping box 1	678 mm x 378 mm x 227 mm	8735.00 g	58.18 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

ADDITIONAL CATALOG INFORMATION

References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.