

Butoject® 897 +



Article no.	897+
Name	Butoject® 897+
Material	butyl
Description	rolled edge roughened, powdered
Length (mm)	350-370
Total thickness (mm)	0,47±0,05
Colour	black
Size	7, 8, 9, 10, 11
Classification	category III EN388:2016 2000 X EN374-1/Type A BCIAKL EN374-5 Virus

FEATURES

- › AQL < 0,65
- › fulfills the requirements of the draft standard for EN 16350:2014-07 for protective gloves against electrostatic hazards: volume resistance <1x10⁸ Ω; test atmosphere: air temperature (23±1)°C, relative humidity (25±5)%; tested by the KCL laborator
- › excellent low degradation
- › good grip by distinct roughened surface
- › offers protection even when sensitivity is needed



APPLICATION

- › printing industry
- › laboratories
- › manufacturing of paints and varnishes
- › chemical industry
- › metal and plastics processing
- › recycling and waste disposal
- › cleaning and maintenance
- › fire brigades and forces

QUALITIES AND ADVANTAGES

- › very good protection against extremely aggressive chemicals
- › excellent wearing comfort
- › very good temperature flexibility
- › good mechanical resistance
- › high tightness against gas



www.kcl.de
sales@kcl.de



by Honeywell

KCL GmbH

Industriepark Rhoen
Am Kreuzacker 9
36124 Eichenzell
Germany
Phone +49 6659 87-300
Fax +49 6659 87-318