

E.506 - Electronic torque / angle adapter



Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Accuracy: - Torque: $\pm 3\%$ between 20% and 100% wrench capacity. - Angle: $\pm 2^\circ$.
- Measuring mode: peak or follower.
- Cycle counter.
- Locking keypad (the operator has access only to program choices and result memorising).
- Measuring unit: N.m, lbf.ft, lbf.in, kg.cm and deg.
- Presetting possible of 9 torque and/or angle values.
- Memory 50 values.
- Supplied in plastic case with calibration certificate.

	Length L [mm]	Capacity [Nm]	Weight [Kg]
E.506-135S	80.0	6.7 - 135	0.268
E.506-200S	80.0	10 - 200	0.268