



Marquardt Mechatronik GmbH  
Schloss-Str. 16  
78604 Rietheim-Weilheim  
Germany

Phone: +49 (0) 7424 / 99-0  
Fax: +49 (0) 7424 / 99-2399  
Net: www.marquardt.de  
E-mail: marquardt@marquardt.de

## Product image / Drawings



Similar to original product

## Technical data

<b>Product number</b>	<b>1045.5502</b>	
Product family	Snap-action switches	
Actuation type	indirect	
Weight	1.600 g	
ROHS conform	yes	
Switching function	Changeover switch (SPDT momentary)	
Material fixed contact	Ag	
Number of poles connections	1 - pole Solder terminal, sealed	
Mechanical life endurance	1E6	
Rating IEC	6 (1) A 250 V AC 30E3	
Design	DIN 41635 B	
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm	
Insulation resistance (new condition)	> 100 (500 V DC) MOhm	
Voltage strength at 250 V	function insulation / basic insulation	1 500 V
	small contact distance	500 V
Proof tracking	250 PTI	
Insulation spacing	acc. to EN 61058 for reinforced or double insulation	
Protection type	Connection Actuator	IP 00 IP 67
Ambient temperature	40 °C	
Ambient temperature	-40 °C ... +100 °C	
Storage temperature	-40 °C ... +100 °C	
Flammability	UL 94 V-0	
Glow wire test temperature	850 °C	
Actuators and additional actuators	actuator: gasket: additional actuator: stainless steel spring steel, L22, lever simulated roller 2.8 long 3.4 wide	
Housing description	PA Latamid glass fiber-reinforced, white natural, 2 lever mounting points	
Connection surface	bearing connection external connection	tinned tinned
Contact material	Ag	
Contact distance	< 3 mm	
Contact type	jump contact	
Operating force	≤ 0.9 N	
Bounce time	< 5 ms	

## Marquardt Products

Difference travel max.	1.3 mm
Pretravel max.	5.3 mm
Overtravel	1.7 mm
Free position (FP) max.	20 mm
Operating position (OP)	16.2 ±1.5 mm
Permissible total travel position	13 mm
Release force	≥ 0.2 N
Approval marks	ENEC 15 / cULus (61058)
Suitable for appliances of protection class	II
EN 60335 cap. 30 conform "G"	yes
Additional labeling	year/week of manuf. acc. to DIN EN 60062
Stock version	●