

压接插针 - SF-08KS010 - 1621571

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



压接插针，车削，触点直径: 0.8 mm，压接范围: 0.08 mm² ... 0.25 mm²


根据接线区域，图示可能有所不同

优势

- ✓ 压接连接：防振和耐高温组装
- ✓ 抗拉扯
- ✓ 接触电阻低
- ✓ 轻松监控生产



关键商业数据

包装单位	100 STK
最小订货量	100 STK
GTIN	 4 046356 937276
GTIN	4046356937276
Sales Key	ABREBJ

技术数据

概述

插拔次数	100
触点连接方式	压接
触点类型	孔式插头


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	环保使用期限 = 50
	更多有害物质的详情，请参考“下载区”内的“制造商声明”

产品图

压接插针 - SF-08KS010 - 1621571

尺寸图



分类

eCl@ss

eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

ETIM

ETIM 4.0	EC000796
ETIM 5.0	EC000796
ETIM 6.0	EC000796

UNSPSC

UNSPSC 13.2	39121522
-------------	----------

附件

附件

压接工具

带数码显示屏的压线钳 - SF-Z0054 - 1615585



压线钳，适用于Ø 0.6 mm / Ø 0.8 mm / Ø 1 mm / Ø 2 mm的车削压接插针，绞线横截面积0.06 mm² ... 2.5 mm²