


Filter regulator PCRP-64-N14-12-C-R1-VC-T31

Part number: 8195731

FESTO



 General operating condition

Data sheet

Feature	Value
Size	64
Series	P
Actuator lock	Adjusting screw with lock
Mounting position	Vertical +/-5°
Grade of filtration	5 µm
Condensate drain	Fully automatic
Design	Filter regulator with pressure gauge
Conforms to standard	NACE MR0175/ISO 15156 (housing and bowl)
Max. condensate volume	30 ml
Controller function	With primary pressure compensation With secondary exhausting
Symbol	00991588
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	Prepared for G1/4
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Pressure regulation range	0.5 bar ... 12 bar
Max. pressure hysteresis	0.02 MPa
Max. pressure hysteresis	0.2 bar
Max. pressure hysteresis	2.9 psi
Max. standard flow rate	2400 l/min
Standard nominal flow rate (standardised to DIN 1343)	1920 l/min
Explosion protection	The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Inert gas
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-10 °C ... 60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [6:4:4]
Media temperature	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Product weight	2285 g
Type of mounting	Inline installation
Pressure gauge connection	G1/4

Feature	Value
Pneumatic connection, port 1	1/4 NPT
Pneumatic connection, port 2	1/4 NPT
Pneumatic connection, port 3	1/8 NPT
Material filter carrier	POM
Note on materials	RoHS compliant
Material mounting bracket	High-alloy stainless steel
Material seals	NBR
Material spring	High-alloy stainless steel
Material filter	Packaging unit
Material housing	Cast stainless steel
Material number housing	1.4409/CF3M(316L)
Material adjusting screw	High-alloy stainless steel
Material bowl	High-alloy stainless steel
Material number of bowl	1.4409/CF3M (316L)