


Features

- For external oscillator
- Loud volume
- Compact dimensions




Basic Condition

Voltage Rating	12 Vp-p
Operating Voltage	1 ... 30 Vp-p
Operating Temperature	-20 ... 70 °C
Storage Temperature Range	-30 ... 80 °C

Electrical Characteristics

Sound Press Level	≥ 85 dB @ 100 mm / 12 Vp-p
Current Consumption	≤ 5 mA @ 12 Vp-p
Resonate Frequency	2.8 kHz +/- 300 Hz
Tone Type	Continuous
Capacitance	28 nF 30% @ 120 Hz
Material	ABS

Measuring Method




Frequency Curve



Piezo Buzzer

Drawing



Art Nr.
RND 430-00033