

Features

- Red LED Beacon
- Steady or Flashing Light
- Temperature -30°C to +50°C
- IP54 Rated
- M16 Cable gland entry
- Polycarbonate plastic offering protection against UV and is Impact resistant

RS PRO RED LED STEADY/FLASHING BEACON FOR INDUSTRIAL APPLICATIONS 12-24VAC/DC

RS Stock No.: 0726244



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Introducing industrial LED beacons from RS PRO, a high quality Steady or flashing beacons ideal for use in a wide range of security and process control applications. This durable Steady or flashing beacon is available in red LED output with an operating voltage or 12 to 24V AC or DC. The units are supplied fully assembled to enable quick and easy installation via screw mount. The simple design allows you to install the beacons to a wall or similar surface with ease. This RS PRO beacon is suitable for light and heavy industrial signalling applications, producing a powerful Steady or flashing light source to signal hazards and emergencies.

General Specifications

Lens	Polycarbonate
Bulb type	LED
Lens Colour	Red
Fitting	Surface / Screw
Housing colour	Grey
Lamp included	Yes
Special features	M16 Cable entry, cable gland supplied

Electrical Specifications

Supply Voltage	12-24VAC/DC
Current Type	AC or DC
Current Consumption	420mA-12V, 215mA-24V

Mechanical Specifications

Dimensions	86 (d) x 90mm (h)
Base Diameter	86mm
Mounting Style	Screw Mount
Weight	0.12kg

Operation Environment Specifications

Maximum Temperature	-30°C
Minimum Temperature	+50°C

Protection Category

IP Rating	IP54
-----------	------

Approvals

Compliance/Certifications	CE / CSA / UL94-V0
Standards Met	EMC (ECE R10), RoHS Compliant