




# SKYTEC® | TRC702

## A LIGHTWEIGHT AND DURABLE PU COATED GLOVE WITH MEDIUM CUT PROTECTION. MADE WITH RECYCLED POLYESTER

TRC702 is a supple and lightweight glove offering a good cut resistant barrier whilst maintaining dexterity and comfort. The flexible PU coating enables a secure grip in greasy and dry conditions. Ideal for handling small components with sharp edges.

### FEATURES

- › Cut resistant: Level C (EN 388:2016)
- › A flexible and comfortable glove offering great dexterity
- › HPPE on the inside provides comfort and protection
- › PU coating gives exceptional abrasion resistance and sensitivity allowing workers to handle small pieces
- › Designed for easy movement and continuous wear
- › Breathable back of hand to reduce perspiration
- › Seamless knit prevents irritation
- › Elasticated wrist provides a secure fit
- › RCS (Recycled claim Standard) certified
- › 1 pair = 1 PET bottle of 500ml recycled



### SUITABLE FOR

#### Typical Industries

- Automotive
- Construction
- Logistics
- Manufacturing
- Utilities

#### Suitable Applications

- Assembly
- Handling sharp and greasy Parts
- Maintenance
- Light fabrication
- Precision Mechanics

### CERTIFICATION



See overleaf for explanation

# SKYTEC® | TRC702

## PRODUCT INFORMATION

MATERIALS	LINER:	13 gauge HPPE, glass fibre, recycled polyester
	COATING:	Polyurethane (PU)
COLOUR	Orange/Black	
LENGTH (mm)	250 (Size Dependent)	
CUFF STYLE	Elasticated knit wrist	

## ORDERING DETAILS

SIZE	CODE	PACKAGING
6/XS	SKG00013GB	10 pairs per bag 120 pairs per case
7/S	SKG00013GD	
8/M	SKG00013GF	
9/L	SKG00013GH	
10/XL	SKG00013GJ	
11/XXL	SKG00013GL	


## RECOMMENDATIONS FOR USE

- **USE:** General handling glove with cut protection. Not suitable for thermal, electrical, chemical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

## CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016 PERFORMANCE LEVELS\*



\*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter

CLASSIFICATION FOR CUT RESISTANCE	
Measured breakthrough time	Permeation performance index (grams)
A1	≥ 200
A2	≥ 500
A3	≥ 1000
A4	≥ 1500
A5	≥ 2200
A6	≥ 3000
A7	≥ 4000
A8	≥ 5000
A9	> 6000

### EUROPE

[www.globusgroup.com](http://www.globusgroup.com)

**E:** [sales@globus.co.uk](mailto:sales@globus.co.uk)  
**T:** +44 (0)161 877 4747  
**F:** +44 (0)161 877 4746

### MIDDLE EAST AND AFRICA

[www.globusgroup.com/gcc](http://www.globusgroup.com/gcc)

**E:** [gcc@globusgroup.com](mailto:gcc@globusgroup.com)  
**T:** +971 4 882 9962  
**F:** +971 4 882 9963



Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM  
 Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

©2023 Globus (Shetland) Ltd | SKY-DATA-TRC702-0623\_1