



Figure similar

RC unit for 5SP4, 2-pole, type AC, In: 100 A, 30 mA, Un AC: 230 V

Model	
product brand name	SETRON
product designation	RCD-unit
design of the product	Instantaneous
product type designation	5SM2
product variations	for 5SP4
General technical data	
number of poles	2
design of pole	2 poles
size of installation devices according to DIN 43880	1
touch protection against electrical shock according to EN 50274	Finger and back-of-hand safe
mechanical service life (operating cycles) typical	10 000
overvoltage category	III
degree of pollution	2
Voltage	
type of voltage of the operating voltage	AC
insulation voltage (Ui) rated value	460 V
surge voltage resistance rated value	4 000 V
tripping fault current rated value	30 mA
operational current	
• at 40 °C rated value	93 A
• at 45 °C rated value	93 A
• at 50 °C rated value	90 A
• at 55 °C rated value	87 A
• at 60 °C rated value	85 A
• at 65 °C rated value	83 A
• at 70 °C rated value	80 A
• at AC rated value	100 A
residual current type	AC
surge current resistance rated value	1 kA
supply voltage	
• at AC	230 V
• for testing equipment minimum	195 V
value range of the supply voltage frequency	50 Hz
value range of the operating frequency	50 Hz
Protection class	
protection class IP	IP20, if the distribution board is installed, with connected conductors
protection function false tripping	Yes

Dissipation	
power loss [W]	
for rated value of the current at AC in hot operating state per pole	6 W
maximum	12 W
Product details	
product feature	
OFF-delay time adjustable	No
rated fault current adjustable	No
sealable	No
Connections	
connectable conductor cross-section solid	
minimum	6 mm ²
maximum	50 mm ²
connectable conductor cross-section stranded	
minimum	6 mm ²
maximum	50 mm ²
tightening torque with screw-type terminals	
minimum	2.5 N·m
maximum	3 N·m
position of power supply cord	top or bottom
Mechanical Design	
height	90 mm
width	71 mm
depth	70 mm
installation depth	70 mm
number of modular width units	4
fastening method	REG
mounting position	any
net weight	535 g
Environmental conditions	
ambient temperature during operation	
minimum	-25 °C
maximum	45 °C
ambient temperature during storage	
minimum	-40 °C
maximum	75 °C
number of test cycles for environmental testing according to IEC 60068-2-30	28
Certificates	
reference code according to IEC 81346-2	F
Approvals Certificates	
General Product Approval	



[Confirmation](#)



General Product Approval	other	Dangerous goods	Environment
Miscellaneous	Confirmation	Miscellaneous	Transport Information
		Environmental Confirmations	

Environment
Environmental Confirmations

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SM2327-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SM2327-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM2327-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

7/5/2024

