



Terminals & Splices > Automotive Terminals



Terminal Type: **Receptacle**

Wire Size: **7 AWG**

Sealable: **No**

Wire Size Search: **7 AWG**

Features

Product Type Features

Sealable	No
----------	----

Contact Features

Crimp Type	F-Crimp
Terminal Type	Receptacle

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Wire Size	7 AWG
Wire Size Search	10.6 mm ²

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	


Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #3-520339-2
ULTRA-FAST 187 ASY REC 16-14 AWG
TPBR



TE Part #CAT-HST-TRSA
TRSA Heat Shrink Tubing



TE Part #1986775-4
SCREWLESS, SW,4P,5.08 PCB, Low
Amp



TE Part #1-917809-3
DYNAMIC D-5 TAB HSG D/R 6P X-X



TE Part #7-1625892-7
3W SM M/OX 5% 18K



TE Part #1-1625885-7
1W SM M/OX 5% 120R



TE Part #1-1123722-3
3.96 EP PLUG HSG 3P(NATURAL)



TE Part #1375820-3
CST-100 II HOUSING 3 POS



Documents

Product Drawings

[TERMINAL,SPARK PLUG STR 7MM](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_34482_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_34482_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_34482_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_34482_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_34482_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_34482_C.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.