

Features

- Bushing with Threaded Blind Hole and base plate: INOX AISI 304 stainless steel (corrosion-resistant, durable).
- Natural Rubber (NR), black color.
- 55 Shore A ± 5 (medium hardness for effective vibration damping).
- Damp vibrations, shocks, and noise from moving bodies or unbalanced vibrating masses.
- Prevents malfunctioning and extends machine lifespan.
- Reduces health risks caused by vibration exposure.
- Minimizes noise pollution.
- Ideal for equipment and machinery where vibration isolation is critical.
- Common in industrial, mechanical, and automation systems.

RS PRO RS PRO Rubber Buffer Bushing with Threaded Blind Hole and Base Plate in INOX AISI 304 Stainless Steel, Vibration-Damper Body in Natural Rubber NR, Black Colour, Hardness 55 Shore A ± 5



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Rubber Buffers Bushing with Threaded Blind Hole and Base Plate – INOX AISI 304 Stainless Steel

The RS PRO range of rubber buffers is designed to absorb vibrations, shocks, and noise in machinery and equipment. These buffers feature a natural rubber (NR) body with a hardness of 55 Shore A \pm 5, combined with INOX AISI 304 stainless steel threaded studs and base plate for excellent corrosion resistance and durability.

What are they used for?

- To isolate vibrations and reduce noise generated by moving parts or unbalanced rotating masses.*
- To protect machinery and surrounding structures from damage caused by shocks and vibrations.*
- To extend equipment lifespan and improve operational stability.*

Applications

Ideal for:

- Industrial machinery*
- Compressors, pumps, and generators*
- HVAC systems*
- Automation and assembly lines*

What are they used with?

Commonly paired with:

- Motors and engines to reduce vibration transmission.*
- Machine frames and bases for stability*
- Sensitive equipment to prevent operational disturbances.*

General Specifications

Material – Metal Parts	INOX AISI 304 Stainless Steel
Material – Buffer Body	Natural Rubber (NR), black color
Hardness	55 Shore A \pm 5
Mounting Type	Bushing with threaded blind hole and Base Plate
Corrosion Resistance	Yes (due to AISI 304 stainless steel)
Noise Reduction	Yes
Shock Absorption	Yes
Applications	Industrial machinery, compressors, pumps, HVAC systems

Similar Products

Stock No.	Diameter (mm)	Length (mm)	Thread Size	Hardness
0713468	8	8	M3	55
0713470	8	13	M3	55
0713471	10	10	M4	55
0713472	10	15	M4	55
0713473	15	15	M4	55
0713474	15	20	M4	55
0713476	20	15	M6	55
0713477	20	20	M6	55
0713478	20	25	M6	55
0713479	20	30	M6	55
0713480	25	15	M6	55
0713926	25	20	M6	55
0713927	25	25	M6	55
0713928	25	30	M6	55
0713929	30	15	M8	55
0713930	30	17	M8	55
0713931	30	20	M8	55
0713932	30	25	M6	55
0713933	30	30	M8	55
0713934	30	40	M8	55
0713935	40	20	M8	55
0713937	40	30	M8	55
0713938	40	40	M8	55
0713939	40	50	M8	55
0713940	40	20	M10	55
0713941	50	20	M10	55
0713943	50	30	M10	55
0713921	50	35	M10	55
0713922	50	40	M10	55

Stock No.	Diameter (mm)	Length (mm)	Thread Size	Hardness
0713923	50	45	M10	55
0713924	50	50	M10	55
0713925	60	30	M10	55
0712815	60	40	M10	55
0712816	60	50	M10	55
0712817	70	30	M10	55
0712818	70	40	M10	55
0712819	70	45	M10	55
0712820	70	55	M10	55
0712821	75	25	M12	55
0712822	75	30	M12	55
0712823	75	40	M12	55
0712824	75	50	M12	55
0712825	75	55	M12	55
0712827	100	40	M16	55
0712828	100	55	M16	55
0712829	100	50	M16	55
0712830	150	75	M20	55
0712831	100	60	M16	55
0712833	125	55	M16	55
0712834	125	75	M16	55
0712835	200	100	M20	55

