

Eaton 135679

Catalog Number: 135679

Eaton Moeller® series E58 Diffuse reflective sensor, Sn=150mm, 4L, 10-30VDC, light, NPN, PNP, M30, metal, M12

General specifications



Product Name	Catalog Number
Eaton Moeller® series E58 Diffuse reflective sensor	135679
	EAN
	4015081324729
Product Length/Depth	Product Height
38.1 mm	38.1 mm
Product Width	Product Weight
38.1 mm	0.23 kg

Certifications

UL Category Control No.: NRKH, NRKH7

CE
UL File No.: E166051
Certified by UL for use in Canada
UL
UL 508
IEC/EN 60947-5-2
CSA File No.: UL report applies to both
US and Canada
CSA-C22.2 No. 14

Product specifications

Type

Optical sensors

Electric connection type

Connector M12

Fitted with:

Background suppression (Perfect Prox)

Enclosure material

Metal

Enclosure type

Cylinder, screw-thread

Operating mode

Switching principle: Light switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Protection against polarity reversal

Short-circuit protection

Reflected-light beam

Protection against wire breakage

Voltage type

DC

Wire size

0

Connection type

4-wire

Plug-in connection M12 x 1

Cable sheath material

Other

Light type

Other

Degree of protection

NEMA 6

IP68

Interface type

Resources

Catalogs

[Product Range Catalog Sensors](#) – products, basic information, applications

Declarations of conformity

[DA-DC-00004652.pdf](#)

[DA-DC-00004657.pdf](#)

Drawings

[eaton-proximity-switches-e58-diffuse-reflective-sensor-dimensions-002.eps](#)

[eaton-proximity-switches-e58-diffuse-reflective-sensor-3d-drawing.eps](#)

Installation instructions

[IL05305003Z](#)

Other

LED indicator

Status indication of Switching state: Red LED

Switch function type

Other

Load current

Max. 100 mA (I_e)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

100 g, Mechanical, Shock duration 3 ms

Optical surface material

Glass

Output current (mA) - max

100 mA

Output current at protected output - max

0 mA

Rated control supply voltage (U_s) at AC, 50 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 50 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at DC - max

30 V

Rated control supply voltage (U_s) at DC - min

10 V

Rated switching distance (S_n)

150 mm

Reflector distance - min

0 mm

Sensor height

0 mm

Sensor length

111 mm

Switching distance - max

165 mm

Switching voltage of OSSD at state high

30 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

312 Hz

Sensing mode

Light switching

Switching output type

PNP/NPN

Sensor material

Stainless steel

Triangulation

Background fade-out

Wavelength of the sensor

660 nm

Width sensor

0 mm

Product category

E58 Harsh Duty Series

Response time

1.6 ms

Adjustment range - max

150 mm

Adjustment range - min

0 mm

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

30 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating distance - max

0 mm

Operating distance - min

0 mm

Adjustment type

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia