





Technical data

NJ2312

Single row cylindrical roller bearings

Single row cylindrical roller bearing, single direction for axial loads, separable, pressed steel cage.

VISUAL (S)



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	60 mm
D - External diameter	130 mm
B - Bearing/Inner ring width	46 mm
E - Upper roller diameter	113 mm
F - Under roller diameter	77 mm
d1 - IR flange outer diameter	84,2 mm
rs - Min fillet radius	2,1 mm
r1s - Min fillet radius	2,1 mm
Radial clearance class	CN
Mass	2,79 kg

PRODUCT PERFORMANCE	
C - Dynamic load	187000000 mN
C0 - Static load	188000000 mN
Cu - Fatigue limit load	22900000 mN
N lim - Oil lubrication limit speed	34200 °/s
N lim - Grease lubrication limit speed	28800 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT	
da min - Min shoulder diameter IR	71 mm
da max - Small face shoulder max diameter	75 mm
dc min - Min inner ring GO diameter	86 mm



ABUTMENT	
Da max - Max shoulder diameter OR	119 mm
ra max - Max fillet radius	2 mm

INDUSTRY CALCUL FACTORS	
Equivalent dynamic radial load	
$P = Fr$	
Equivalent static radial load	
$P_0 = Fr$	