

SVS Eco valve plug A-18mm screw terminal

 2-pol. + FE, 0,5 - 1,5mm², 4 - 6mm, LED+VDR 24V

Art.No.: 7000-29006-0000000

Weight: 0.028

Country of origin: HU

Model designation: MSVSE-EB1X-M16 SVS Eco LED

Form A (18 mm)

 24 V AC/DC $\pm 15\%$




LED and VDR

metric

field-wireable

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
Illustration


Product may differ from Image


Side 1

Mounting method	inserted, screwed
Degree of protection (EN IEC 60529)	IP65
Commercial data	
ECLASS-6.0	27279221
ECLASS-6.1	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440105
ECLASS-10.1	27440105
ECLASS-11.1	27440105
ECLASS-12.0	27440105
ETIM-5.0	EC002062
customs tariff number	85366990
GTIN	4048879431972
Packaging unit	1
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage AC min.	20,4 V
Operating voltage AC max.	26,4 V
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	26,4 V
Current operating per contact max.	1,5 A
Diagnostics	
Status indication LED	yellow
Installation	
Connection cross section min.	0,5 mm ²
Connection cross section max.	1,5 mm ²
Installation Connection	
Tightening torque	0,4 Nm
Tightening torque clamping screw	0,2 Nm
Mounting set	M16 x 1.5
Installation Pin assignment	
No. of poles	2 + PE
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Additional suppressor	Varistor
Mechanical data Material data	
Color housing	opaque
Material gasket	NBR
Material housing	PA
Mechanical data Mounting data	
fastening screw	M3
Clamping range min.	4 mm
Clamping range max.	6 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	90 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Note on bending radius

Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.