



S100 Digital USB Shipping Scale



100 kg Digital USB Shipping Scale

- Rugged, heavy-duty, portable digital shipping scale weighs parcels and packages up to 100 kg
- Built-in wrap-around handle for easy portability – allows you to carry the scale to heavy packages, not vice-versa
- Detachable LCD screen allows convenient hand-held or wall-mounted viewing
- Displays weight in an accurate, easy-to-read digital format – in kg/g (0.0 kg) or lbs/oz (0.0 lb oz)
- “Hold” feature locks weight display for ten seconds after package is removed – convenient when large package blocks view of display
- Tare function – weigh items in a container minus weight of container
- Automatic shut-off when scale not in use – prolongs battery life
- 40 cm x 41.5 cm size (30 cm x 30 cm weighing platform) accommodates large packages
- Powered by AC adapter (included), 3 AAA batteries (not included), or USB cable (included) connected to PC or Mac®
- Work with Windows Vista®, Windows® 7, Windows® 8 or Mac OS® X 10.5 or later - Intel® only



FREE
Software*

* available to read weight from your PC or Mac® – visit www.dymo.com

Single Unit Includes:

- S100 Digital USB Shipping Scale
- USB Cable
- AC Adapter
- Manual



Quick Specs	
Unit Dimensions (H x W x L)	415 x 400 x 49 mm
Weight (excluding cable)	4 kg
Mac®/PC Compatible	Yes
Adapter	Charges via USB Cable (included) or Adapter (included) or 3 AAA batteries (not included)
Max. Weight	100 kg
Platform Dimensions	30 x 30 cm
Weight Interval	0.1 kg
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price
S0929060	S100 USB Shipping Scale 100KG UK	Unit	9.2	44.6	46.5	4.4	1	3501170929063	
		Shelf	-	-	-	-	-	-	
		Case	48.5	20.4	46.0	9.5	2	13501170929060	
		Pallet	120.0	80.0	107.0	158.4	28	-	

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM

13-0103

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A **NewellRubbermaid** Brand

©2014 Newell Europe LLC

A Newell Rubbermaid Company™	SCHAWK! <small>RAZ Miraris Business Park Campus - 2, 5th Floor No. 143, D.M. G. R. Road Kandanchavadi Chennai 600 098 India T +91 44 4219 7777 www.schawk.com</small>	<div><div>Cyan</div><div>Magenta</div><div>Yellow</div><div>Black</div></div>	Use the PANTONE MATCHING SYSTEM for accurate color reproduction	
	VERSION	JOB DESCRIPTION : NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters FILE NAME : DY_1362812_2014_EMEA_S100_TechSheet_V3.indd		BRAND : DYMO
	3 Date: 10-09-2014 Operator : MKS	<div><div>SCHAWK JOB # : 310253M</div><div>NRM JOB # : 1362812</div><div>SAP / FG # : N/A</div><div>COMPONENT # : N/A</div><div>NO. OF PAGES# : 1</div><div>DIELINE : N/A</div><div>UPC : N/A</div><div>VENDOR : N/A</div></div>		
	Note :			