Printing date 04.08.2017

Version: 1

Revision: 04.08.2017

Frinting date 04.08.2017	version. 1	Revision. 04.08.2017
SECTION 1: Identification of th	he substance/mixture and of the company/und	lertaking
1.1 Product identifier		
· Trade name: Zep Commercial® Tar &	Bitumen Remover	
Sector of Use SU21 Consumer uses: Private househo	tance or mixture and uses advised against Ids / general public / consumers n (administration, education, entertainment, services, cra	(fismen)
· Application of the substance / the mixtu		fishen
 1.3 Details of the supplier of the safety of Manufacturer/Supplier: ZEP UK Ltd Tanhouse Lane Widnes Cheshire, WA8 0RR United Kingdom Tel: +44 (0)151 422 1000 Fax: +44 (0)151 422 1011 @: info@zep.co.uk web: www.zep.co.uk 		
ZEP Industries BV Vierlinghweg 30 4612 PN Bergen op Zoom The Netherlands Tel: (NL) + 31 164 250 100 (B) + 32 2 Fax:(NL) + 31 164 266 710 (B) + 32 2 3 @: sales@zepbenelux.com		
ZEP ITALIA SRL Via Netunese Km. 25.000 04011 Aprilia (LT) - Italy Tel: +39.06.926691 Fax: +39.06.92747061 @: tecnico@zepeurope.com Sito: www.zep.it		
Further information obtainable from: Customer Service NL: Tel: + 31 164 250 100 Fax: + 31 16 B: Tel: + 32 2 347 0117 Fax: + 32 2 347 IT: Tel: + 39 069 266 91Fax: + 39 06.92 UK: Tel: +44 151 422 1000 Fax: + 44 1.5 1.4 Emergency telephone number: Customer Service NL: Tel: + 31 164 250 100 Fax: + 31 16 B: Tel: + 32 2 347 0117 Fax: + 32 2 347 IT: Tel: + 31 164 250 100 Fax: + 31 16 B: Tel: + 32 2 347 0117 Fax: + 32 2 347 IT: Tel: + 39 069 266 91Fax: + 39 06.92 UK: Tel: +44 151 422 1000 Fax: +44 1.5	7 1395 7 470 61 51 422 1011 64 266 710 7 1395 7 470 61	
SECTION 2: Hazards identifica		
Classification according to Regulation Asp. Tox. 1 H304 May be fatal if swallo	(EC) No 1272/2008	
• 2.2 Label elements • Labelling according to Regulation (EC) The substance is classified and labelled • Hazard pictograms		



· Signal word Danger

Printing date 04.08.2017

Version: 1

Revision: 04.08.2017

Trade name: Zep Commercial® Tar & Bitumen Remover

	(Contd. of pa
	ining components of labelling:
	C11-C14, n-alkanes, isoalkanes, cyclics, $<2\%$ aromatics
· Hazard stateme	
2 0	ital if swallowed and enters airways.
· Precautionary s	statements
P102	Keep out of reach of children.
P301+P310	IF SWALLOWED: Immediately call a doctor.
P301+P330+P	331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302+P352	IF ON SKIN: Wash with plenty of water/and soap
P305+P351+P	338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy
	do. Continue rinsing.
P337+P313	<i>If eye irritation persists: Get medical advice/attention.</i>
• Additional info	rmation:
EUH066 Repea	ted exposure may cause skin dryness or cracking.
· 2.3 Other hazar	rds The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds.
· Results of PBT	and vPvB assessment
· PBT: Not appli	cable.
· vPvB: Not appl	icable.

SECTION 3: Composition/information on ingredients

- 3.2 Chemical characterisation: Mixtures

• Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous components:

 EC number:
 926-141-6
 Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics</th>
 75-100%

 Reg.nr.:
 01-2119456620-43
 \$ Asp. Tox. 1, H304
 75-100%

Ingredients according to Detergents Regulation 648/2004/EC

For the wording of the listed hazard phrases refer to section 16.

Aliphatic hydrocarbons

SECTION 4: First aid measures

• 4.1 Description of first aid measures

- General information: Immediately remove any clothing soiled by the product.
- After inhalation: Supply fresh air; consult doctor in case of complaints.
- After skin contact:

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

• After eye contact: Rinse opened eye for several minutes under running water. Then consult a doctor.

• After swallowing: Do not induce vomiting; call for medical help immediately.

4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.

• 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

· Suitable extinguishing agents: CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

• 5.2 Special hazards arising from the substance or mixture No further relevant information available.

· 5.3 Advice for firefighters

· Protective equipment: No special measures required.

SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures Wear protective equipment. Keep unprotected persons away. Ensure adequate ventilation
- 6.2 Environmental precautions: Do not allow to enter sewers/ surface or ground water.
- 6.3 Methods and material for containment and cleaning up: Absorb with liquid-binding material (sand, diatomite, universal binders). Dispose contaminated material as waste according to item 13.

(Contd. on page 3)

≥30%

Printing date 04.08.2017

Version: 1

Revision: 04.08.2017

(Contd. of page 2)

Trade name: Zep Commercial® Tar & Bitumen Remover

6.4 Reference to other sections

See Section 7 for information on safe handling. See Section 8 for information on personal protection equipment. See Section 13 for disposal information.

SECTION 7: Handling and storage

• 7.1 Precautions for safe handling Use only in well ventilated areas.

• Information about fire - and explosion protection: No special measures required.

- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:

• Requirements to be met by storerooms and receptacles: Provide solvent resistant, sealed floor.

- Information about storage in one common storage facility: Not required.
- Further information about storage conditions: None.

• 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

• Additional information about design of technical facilities: No further data; see item 7.

· 8.1 Control parameters

\cdot Ingredients with limit values that require monitoring at the workplace:	
34590-94-8 (2-methoxyme	ethylethoxy)propanol (2.5-5%)
	Long-term value: 308 mg/m³, 50 ppm Sk
IOELV (European Union)	Long-term value: 308 mg/m³, 50 ppm Skin

• Additional information: The lists valid during the making were used as basis.

- · 8.2 Exposure controls
- · Personal protective equipment:
- General protective and hygienic measures: Keep away from foodstuffs, beverages and feed. Wash hands before breaks and at the end of work.
- *Respiratory protection:*
- Filter AX
- Not necessary if room is well-ventilated.
- Protection of hands:



Protective gloves

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

• Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed. The determined penetration times according to EN 374 part III are not performed under practical conditions. Therefore a maximum wearing time, which corresponds to 50% of the penetration time, is recommended.

For the permanent contact gloves made of the following materials are suitable: Nitrile rubber, NBR

PVA gloves

· Not suitable are gloves made of the following materials: Strong material gloves

· Eye protection: Goggles recommended during refilling

· Body protection: Solvent resistant protective clothing

(Contd. on page 4)

Version: 1

Revision: 04.08.2017

Trade name: Zep Commercial® Tar & Bitumen Remover

(Contd. of page 3)

SECTION 9: Physical and chem	ical properties
• 9.1 Information on basic physical and c • General Information • Appearance:	hemical properties
Form:	Liquid
Colour:	Colourless
· Odour:	Solvent-like
· Change in condition Melting point/freezing point: Initial boiling point and boiling range	Undetermined. r: 189°C
· Flash point:	67°C
· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	230°C
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
• Explosive properties:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	0.6 Vol %
Upper:	6 Vol %
· Vapour pressure at 20°C:	0.1 hPa
· Density at 20°C:	$0.8 g/cm^3$
Relative density	Not determined.
Vapour density	Not determined.
Evaporation rate	Not determined.
· Solubility in / Miscibility with	
water:	Insoluble.
Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	100.0 %
Swiss VOC:	3.00 %
Solids content:	0.0 %
9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

· 10.1 Reactivity No further relevant information available.

- 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- · 10.3 Possibility of hazardous reactions No dangerous reactions known.
- 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- 10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

· 11.1 Information on toxicological effects

· Acute toxicity Based on available data, the classification criteria are not met.

· LD/LC50 values relevant for classification:

Hydrocarl	Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics	
Oral	LD50	>5,000 mg/kg (Rat) (OECD 401)
Dermal	LD50	>5,000 mg/kg (Rabbit) (OECD 402 (24 h))

(Contd. on page 5) GB

Printing date 04.08.2017

Version: 1

Revision: 04.08.2017

(Contd. of page 4)

Trade name: Zep Commercial® Tar & Bitumen Remover

Inhalative LC50/8 h >5,000 mg/m3 (Rat) (OECD 403) Primary irritant effect:

- Skin corrosion/irritation Based on available data, the classification criteria are not met.
- · Serious eye damage/irritation Based on available data, the classification criteria are not met.
- Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- Carcinogenicity Based on available data, the classification criteria are not met.
- Reproductive toxicity Based on available data, the classification criteria are not met.
- STOT-single exposure Based on available data, the classification criteria are not met.
- STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard
- May be fatal if swallowed and enters airways.

SECTION 12: Ecological information

· 12.1 Toxicity

· Aquatic toxicity:

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics

EL50 (48 h) >1,000 mg/l (Daphnia magna (water flea)) (OECD 202)

OECD test 301 F 69 % (biodegradation in % after 28 days)

Readily Biodegradable

- · 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.
- 12.4 Mobility in soil No further relevant information available.
- Additional ecological information:
- General notes: Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.
- · 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation Smaller quantities can be disposed of with household waste.
- · Uncleaned packaging:
- Recommendation: Disposal must be made according to official regulations.

14.1 UN-Number ADR, IMDG, IATA	Void	
14.2 UN proper shipping name ADR, IMDG, IATA	Void	
14.3 Transport hazard class(es)		
ADR, IMDG, IATA Class	Void	
14.4 Packing group ADR, IMDG, IATA	Void	
14.5 Environmental hazards:	Not applicable.	
14.6 Special precautions for user	Not applicable.	
14.7 Transport in bulk according to Annex II of the IBC Code	Marpol and Not applicable.	

Printing date 04.08.2017

Version: 1

Revision: 04.08.2017

(Contd. of page 5)

Trade name: Zep Commercial® Tar & Bitumen Remover

· UN "Model Regulation":

Void

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture Reg. (EC) n. 1272/2008 - CLP;
Reg. (EC) n. 1907/2006 - Reach;
Reg. (EC) n. 2015/830 annex II of REACH;
Reg. (EC) n. 648/04 (Detergents);
Reg. (EC) n. 528/12 (Biocides BPR);
Reg. (EC) n. 1223/2009 (Cosmetics);
Dir. 06/08 ADR - RID - IMDG - IATA;
Dir. 47/08 (Aerosols); Dir. 12/18 (Seveso III);
Dir. 2008/98/CE and Reg. (EC) n.1357/2014 (Waste management)

· Directive 2012/18/EU

• Named dangerous substances - ANNEX I None of the ingredients is listed.

• REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3

· National regulations:

· Technical instructions (air):

Class	Share in %
NK	75-100

· Waterhazard class: Water hazard class 1 (Self-assessment): slightly hazardous for water.

• 15.2 Chemical safety assessment: A Chemical Safety Assessment has been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H304 May be fatal if swallowed and enters airways.

· Department issuing SDS:

Customer Service NL: Tel: + 31 164 250 100 Fax: + 31 164 266 710 B: Tel: +32 2 347 0117 Fax: +32 2 347 1395 IT: Tel: +39 069 266 91Fax: +39 06.927 470 61 UK: Tel: +44 151 422 1000 Fax: +44 151 422 1011 Contact: Customer Service NL: Tel: + 31 164 250 100 Fax: + 31 164 266 710 B: Tel: +32 2 347 0117 Fax: +32 2 347 1395 IT: Tel: +39 069 266 91Fax: +39 06.927 470 61 UK: Tel: +44 151 422 1000 Fax: +44 151 422 1011 Abbreviations and acronyms: ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods

International Maritime Code for Dangerous Goods
 IMDG: International Maritime Code for Dangerous Goods
 IATA: International Air Transport Association
 GHS: Globally Harmonised System of Classification and Labelling of Chemicals
 EINECS: European Inventory of Existing Commercial Chemical Substances
 ELINCS: Chemical Abstracts Service (division of the American Chemical Society)
 LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Asp. Tox. 1: Aspiration hazard – Category 1

(Contd. on page 7)

GB

Version: 1

Revision: 04.08.2017

Trade name: Zep Commercial® Tar & Bitumen Remover

(Contd. of page 6)

A	nnex: Exposure scenario
SI	ort title of the exposure scenario
	r the finished product.
	p Commercial® Tar & Bitumen Remover
	ctor of Use
	121 Consumer uses: Private households / general public / consumers
	122 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
	escription of the activities / processes covered in the Exposure Scenario See section 1 of the annex to the Safety Data Shee
С	onditions of use
	uration and frequency 5 workdays/week.
Pl	ysical parameters
	ysical state Fluid
С	ncentration of the substance in the mixture The substance is main component.
U	ed amount per time or activity
	cording to directions for use.
Sn	naller than 10 g per application.
0	her operational conditions
	her operational conditions affecting environmental exposure No special measures required.
	her operational conditions affecting consumer exposure Keep out of the reach of children.
	her operational conditions affecting consumer exposure during the use of the product Not applicable.
	sk management measures
	orker protection
	ganisational protective measures No special measures required.
	chnical protective measures Ensure that suitable extractors are available on processing machines
	rsonal protective measures
	o not inhale gases / fumes / aerosols.
	otective gloves
	lection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
	easures for consumer protection Ensure adequate labelling.
	wironmental protection measures
	ater No special measures required.
	sposal measures Ensure that waste is collected and contained.
	sposal procedures Must not be disposed together with household garbage. Do not allow product to reach sewage system.
	aste type Partially emptied and uncleaned packaging
G	<i>iidance for downstream users</i> No further relevant information available.