



Pony Testing International Group

I、SAMPLE DESCRIPTION

Sample description		Li-ion Battery		Sample model	AS102040
Applicant		SHENZHEN A&S POWER TECHNOLOGY CO LTD			
Manufacturer	Name	Dongguan Golden Cel Battery Co., Ltd			
	Address	No.11, YinHu Industrial Park, JiaoYiTang Village, TangXia DongGuan Guangdong, China			
	Tel	+86-755-2816 9348			
	E-mail	pub@szaspower.com	Web	---	
Nominal voltage		3.7V	Rated capacity	0.7Ah	Limited charge voltage 4.2V
Charge current		0.35A	Maximum continuous charge current	0.7A	End charge current 0.014A
Cut-off voltage		3.0V	Maximum discharge current	0.7A	Mass 13.185g
Cell number		1PCS	Cell model	AS102040	Cell capacity 0.7Ah
Manufacturer of cell		DONG GUAN GOLDEN CEL BATTERY CO LTD			
Electrochemistry System		Li-Co			
Entrust date		2019-03-01		Finished date	2019-03-15

II、TEST METHOD

UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria (ST/SG/AC.10/11/Rev.6/Amend.1), Part III sub-section.

III、TEST ITEM & CONCLUSION

ITEM	SAMPLE NUMBER	STANDARD	CONCLUSION
Altitude simulation	N1~N5 C1~C5	UN38.3 ST/SG/AC.10/11/Rev.6/ Amend.1	PASS
Thermal test			PASS
Vibration			PASS
Shock			PASS
External short circuit			PASS
Crush	N6~N10 C6~C10	UN38.3 ST/SG/AC.10/11/Rev.6/ Amend.1	PASS
Overcharge	N11~N14 C11~C14		PASS
Forced discharge	N15~N24 C15~C24		PASS

The Samples has passed the test items of UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria (ST/SG/AC.10/11/Rev.6/Amend.1), Part III sub-section.

Appraiser: Zhou Xiang zhu Checker: Jinshifang

Approver: Yishawbn

Issue Date: March 15, 2019