

## MultiSync® E241N LCD 24" Commercial Display

### Datasheet



#### NEC MultiSync® E241N Ultra-Thin Bezel - The Office Workhorse, combining sleek and elegant design with health-conscious performance

The 24" ultra-thin bezel display targeting reliable office productivity, performance and quality, fulfils demand for future-ready design. Enduring productivity requires high attention to healthcare. Ensuring the well-being of the user, built-in Low Blue Light technology filters out hazardous blue light emissions whilst Flicker-Free technology eliminates the effect of flickering. The users' eyes are protected whilst ensuring a true-to-life display colour performance from all viewing angles. The LED backlight panel with AH-IPS technology supports a high display brightness of 250 cd/m<sup>2</sup> and in parallel lowers power consumption.

The ultra-narrow bezel display reduces the display footprint without compromising on screen size and gives an office a fresh professional interior with its sleek and elegant design.

### Benefits

**Future-Ready Design** – best in form and function design with 3-sided 1 mm ultra-thin bezel gives an office a fresh professional interior.

**Protecting your eyes from strain and damage** – Built-in Low Blue Light technology filters out hazardous blue light emissions whilst Flicker-Free technology eliminates any backlight flickering, thus protecting your eyes against cataracts and macular degeneration without compromise to true-to-life display colour performance.

**Das ergonomische Büro** – Die umfassende Höhenverstellbarkeit (110 mm), Schwenk-, Neige- und Pivotfunktion sorgen für die individuelle und passgenaue ergonomische Ausrichtung.

**Business Class Image Quality** – Advanced High-Performance IPS (AH-IPS) panel provides the very best viewing angles as well as noticeably better colour reproduction.

**Your environmental and social responsibility** – NEC's TCO 7 and ENERGY STAR 7 certified display is environmentally designed with minimal hazardous material meeting the growing demand for more sustainable technologies.

## Product Information

Product Name	MultiSync® E241N
Product Group	LCD 24" Commercial Display
Order Code	60004221 (WH) , 60004222 (BK)

## Display

Panel Technology	IPS TFT with W-LED backlight
Screen Size [inch/cm]	24 / 60
Screen Aspect Ratio	16:9
Pixel Pitch [mm]	0.275
Brightness (typ.) [cd/m <sup>2</sup> ]	250
Contrast Ratio (typ.)	1000:1
Viewing Angle [°]	178 horizontal / 178 vertical (typ. at contrast ratio 10:1)
Response Time (typ.) [ms]	6
Colours [Mio.]	16.77

## Synchronisation Rate

Horizontal Frequency [kHz]	31.5 - 81.1
Vertical Frequency [Hz]	56 - 76

## Resolution

Optimum Resolution	1920 x 1080 at 60 Hz
--------------------	----------------------

## Connectivity

Digital	1 x DisplayPort; 1 x HDMI
Analog	1 x mini D-sub 15 pin

## Electrical

Power Consumption on Mode [W]	16 (Eco Mode 1); 18 (typ.); 28 (max.)
Power Savings Mode [W]	0.29
Power Supply	integrated power supply

## Environmental Conditions

Operating Temperature [°C]	+5 to +35
Operating Humidity [%]	20 to 80

## Ergonomics

Height adjustable stand [mm]	110
Screen Tilt [°]	5 to 25
Screen Swivel [°]	45 to 45
Screen Rotate [°]	0 to 90 (landscape to portrait mode)

## Mechanical

Bezel Width [mm]	1 (left and right); 1 (top)
Dimensions (W x H x D) [mm]	538.6 x 373.9 x 213.9
Weight [kg]	With stand: 5.5
VESA Mounting [mm]	100 x 100

## Additional Features

Special Characteristics	DisplayPort; EcoModes
Colour Versions	Black Front Bezel, Black Back Cabinet; White Front Bezel, White Back Cabinet
Cable Management	yes
Plug and Play	VESA DDC2Bi
Audio	1W + 1W (De-activateable); Headphone Jack
Adjust Functions	Auto Adjust; Brightness; Carbon Footprint Meter / Carbon Savings Meter; DV Mode; EcoMode; Language Select
Shipping Content	Power Cable; Setup Guide Signal Cable: DisplayPort; VGA - VGA
Safety and Ergonomics	EnergyStar 7.0; Flicker-free; Low Blue Light; RoHS; TCO 7.0; TÜV Ergonomics; TÜV GS; WEEE

## Green Features

Energy Efficiency	Carbon Footprint Meter / Carbon Savings Meter; ECOMode; Energy efficiency class: A+
Ecological Standards	Energy Star 7.0; RoHS compliant; TCO 7.0; WEEE



RoHS



TÜV  
Ergonomics



TÜV GS

This document is © 2018 NEC Display Solutions Europe GmbH.

All rights reserved in favour of their respective owners. All hardware and software names are brand names and/or registered trademarks of the respective manufacturers. All specifications are subject to change without notice. Errors and omissions are excepted. 08.06.2018