

TECHNICAL DATA SHEET

Update of this document : 07-02-2018
Référence ISO de ce document : DON/LS 03.1089.B



LEMAITRE

LEMAITRE SECURITE SAS

17 rue Bitschhoffen
CS 90024

F 67350 La Walck FRANCE

Tél. : +33 (0)3 88 72 28 80

Fax : +33 (0)3 88 07 05 37

www.lemaitre-securite.com

contact@lemaitre-securite.com






VITAMINE HIGH BLACK S3 SRC

HIGH SHOE IN WATER-REPELLENT

SUEDE LEATHER SPLIT

PROTECTIONS FOR THIS MODEL



Sizes available : from 35(2) to 42(8)

Weight of one pair in size 37 (4): 880 gr.

Norme EN ISO 20345 : 2011

CERTIFICATION N°: 0161/18661/12

Upper features

- Upper : water-repellent suede leather
- Tongue : water-repellent suede leather
- Quarter lining : black three-dimensional micro-porous textile
- Vamp lining : synthetic
- Backpart : synderm
- Closing : metallic eyelets
- Laces : polyamid
- Tongue markings : size, manufacturer, manufacture date (month, year), norm, protection, CE marking.

Protections

- Toecap : steel (200 joules)
- Anti-perforation insert : stainless steel (1100N)

Fitting features

- Natur'form (large)
- Lasting : California
- Lasting insole : texon
- Footbed : foam and textile

Sole features

- Name : PARABOLINE
- Material : dual density polyurethane
- Comfort sole density : 0,5
- Comfort sole color : dark grey
- Outsole density : 1
- Outsole color : black
- Slip resistance SRA (flat) : 0,45 ; (heel) : 0,42
- Slip resistance SRB (flat) : 0,22 ; (talon) : 0,18

Basics and additional requirements of the norm EN ISO 20345

Steel toecap Polycarbonate toecap Aluminium toecap (200 joules)

Steel midsole Non-metallic midsole

A Electric resistance – Antistatic shoes.

Ci Insulating sole against cold.

E Heel energy absorption.

Fo Hydrocarbons resistance of the undermine sole.

Hi Insulating sole against heat.

HRO Heat resistance of the sole.

M Metatarsal protection.

P Perforation resistance.

Wru Water repellent upper.

Wr Water resistant footwear.



Regarding the norm EN ISO 20345, the minimum results for slip resistance to get the SRC certificate are :
SRA (flat) \geq 0,32
SRA (heel) \geq 0,28
SRB (flat) \geq 0,18
SRB (heel) \geq 0,13

Advantages = End users benefits

**Trendy safety shoe for women
with 100% composite protections.**

→ **Well fitting adapted to the morphology of the female foot.**

→ **Water-repellent suede leather** : leather in trendy colors, noble and very strong material which helps to fight against water infiltration.

→ **Three-dimensional micro-porous textile as lining** : High breathability thanks to its structure that allows better ventilation of sweat. It is flexible and it improves comfort.

→ **Polyurethane with good properties** : good antistatic properties and good resistance to hydrolysis and heat.

→ **PARABOLINE sole** :

- ✓ **Slip resistant sole** thanks to a structured drawing, which allows a quick evacuation of liquids.
- ✓ **Special design to suit the shape of women's feet for a better fit.**
- ✓ Polyurethane Double Density (PU2D) injected : **the best dual density polyurethanes** for the insole and outsole.

→ **PARABOLIC® sole** :

- ✓ **Exceptional grip** : the concave structure of the sole allows progressive bending of the sole in order to optimize grip.
- ✓ **Comfort when walking** : the spring effect gives a more dynamic walk and facilitates walking.
- ✓ **Anti-fatigue** : with every step, the recycled energy gives you a spring in your step and provides anti-fatigue effect to your legs.