

Features

- Multi AC Head
- DOE Level VI Efficiency
- 2.1 DC Connector
- Worldwide Approvals
- 22 Watts
- 4 x AC Heads included

RS PRO AC/DC Adapters

RS Stock No.: 0360643



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

AC/DC Adapters

Product Description

This compact 9vdc 22watt Multi AC Head power supply is suitable for worldwide use with a maximum load of 2.5 amps

- UK, EU, US, & AUZ AC Heads included
- 2.1 C+ve DC Connector

General Specifications

Type	Switched Mode Power Supply
Input Plug Type	UK, EU, US & AUZ
Output Connector	2.1x5.5x12mm C+ve
Input Connector	Selectable
Cable Length	1.5mtr
Cable Type	2 core Fig 8
Power Indicator	No
Over Current Protection	Yes
Short Current Protection	Yes
Over Current Protection	Yes
MTBF	50000 hours at maximum load
Medical Approval	No

Electrical Specifications

Input Specifications	
Rated Input Voltage	100 to 240V ac
Full Input Voltage Range	90 – 264V ac
Rated Frequency	50/60Hz
Full Frequency Range	47/63Hz
Efficiency	81%
Input Current (RMS Max.)	0.6A
Inrush Current	40A Max
Leakage Current (max.)	0.25mA / 240V ac
Input Protection	Thermal fuse in Primary; Current Limit, Short Circuit

Output Specifications		
Output Voltage	9V dc	
Maximum No load Voltage	9V dc	
Output Maximum Current	2.5amp	
Output Minimum Current	0A	
Output Regulation	+/-5%	
Rated Power	22.5W	
Start Up Delay	20ms	
Start Up Rise Time	20ms	
Hold Up Time	20ms	
Number of Outputs	1	
Efficiency	81%	
Efficiency Level	VI	
Output Voltage Precision	5%	
Ripple & Noise	200mV	
Turn On Delay	4 Seconds Max.	
Insulation Class	II	
Switching Frequency	70KHz	
Isolation Resistance	100MΩ @500V dc	
Voltage Isolation	Input-Output	3000V ac
	Input-Ground	
	Output-Ground	

Mechanical Specifications

Dimension	
Length	71mm
Width	43mm
Depth	31mm
Weight	110g





AC/DC Adapters

Operation Environment Specifications

Operating Humidity	20% to 85% RH non-condensing
Cooling	Natural convection
Operating Temperature Range	0 to 40°C
Storage Temperature Range	-20 to 80°C
Altitude During Operation	3000m
Vibration Resistance	To IEC-68-2-6

Approvals


Compliance/Certifications	<u>CE/UKCA/UK/RCM</u>
Declarations	MFR Declaration of Conformity
Medical Approval	NO




American wire
gauge



Australian
standard



British system



European
standard