



2

YEARS
MANUFACTURER
GUARANTEE

700
+100
LUMEN

IP 54

10h
MAX

360°

USB RECHARGEABLE

Product number1175640010

EAN4007123691241

TECHNICAL DATA

Luminous flux	700 lm	Number of batteries	1
Total luminous flux secondary source	100 lm	Battery type	Built-in battery pack
Colour temperature	5700 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Impact strength	IK07
Battery capacity	2 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP54
Light duration max.	10 h	Colour	black
Battery charging time approx.	3.5 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.36 kg
Weight of product (without packaging)	0.23 kg	Dimension LxWxH (incl. packing)	8.7 cm x 6.2 cm x 27.8 cm
Dimension LxWxH (without packing)	5.8 cm x 3.2 cm x 20.1 cm		